

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739105

Luminaire Tested: LD4D02D010-EU4DR300210IC9035-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P739105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR300210IC9035-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 272.9 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739105
CATALOG NUMBER: LD4D02D010-EU4DR300210IC9035-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P739105

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9035-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	67152	67152	67152
5°	65226	65149	65226
10°	56490	56094	56482
15°	36856	36666	36476
20°	18328	19020	18303
25°	9231	10413	9045
30°	3694	4022	3217
35°	1710	1645	1374
40°	739	829	699
45°	520	649	530
50°	179	476	191
55°	107	200	107
60°	77	92	77
65°	54	54	54
70°	22	22	22
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 649 cd/sqm



TEST NUMBER: P739105

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9035-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.1	28.3
10°-20°	124.2	45.5
20°-30°	53.7	19.7
30°-40°	12.2	4.5
40°-50°	4.2	1.5
50°-60°	1.0	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.1	93.5
0°-40°	267.3	98.0
0°-60°	272.5	99.9
0°-90°	272.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	877	877	877	877	877	
5°	849	848	848	850	849	77
15°	465	460	463	461	460	125
25°	109	113	123	111	107	52
35°	18	19	18	17	15	12
45°	5	6	6	6	5	3
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P739105

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9035-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	877.3	877.3	877.3	877.3	877.3
2.5°	871.5	870.9	871.2	871.6	871.8
5°	848.9	848.0	847.9	849.6	848.9
7.5°	803.2	802.1	800.3	804.3	808.1
10°	726.8	725.5	721.7	723.6	726.7
12.5°	614.0	609.8	609.8	615.8	615.0
15°	465.1	459.5	462.7	461.1	460.3
17.5°	312.8	310.7	314.8	313.5	308.1
20°	225.0	225.6	233.5	229.5	224.7
22.5°	164.2	166.2	175.6	165.4	161.6
25°	109.3	113.4	123.3	110.6	107.1
27.5°	67.2	69.2	79.1	66.3	64.5
30°	41.8	40.9	45.5	39.1	36.4
32.5°	27.4	26.2	27.7	24.9	22.7
35°	18.3	18.7	17.6	17.4	14.7
37.5°	11.5	13.2	11.6	12.4	9.5
40°	7.4	9.6	8.3	9.1	7.0
42.5°	6.1	7.4	6.8	7.2	6.2
45°	4.8	6.0	6.0	6.0	4.9
47.5°	2.7	4.0	5.1	4.1	2.9
50°	1.5	2.0	4.0	2.1	1.6
52.5°	1.0	1.1	2.7	1.2	1.1
55°	0.8	0.8	1.5	0.9	0.8
57.5°	0.6	0.6	0.8	0.6	0.6
60°	0.5	0.5	0.6	0.5	0.5
62.5°	0.3	0.3	0.4	0.3	0.3
65°	0.3	0.3	0.3	0.3	0.3
67.5°	0.1	0.2	0.2	0.2	0.2
70°	0.1	0.1	0.1	0.1	0.1
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)