

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746613

Luminaire Tested: LD4D30D010-EU4DR7020359027-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P746613
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR7020359027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1617.2 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746613

CATALOG NUMBER: LD4D30D010-EU4DR7020359027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P746613

CATALOG NUMBER: LD4D30D010-EU4DR7020359027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	198658
5°	192759
10°	187377
15°	184932
20°	172677
25°	129730
30°	91708
35°	32492
40°	17073
45°	18187
50°	18834
55°	19201
60°	19317
65°	18899
70°	17858
75°	16506
80°	14661
85°	11909

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 19318 cd/sqm



TEST NUMBER: P746613

CATALOG NUMBER: LD4D30D010-EU4DR7020359027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.8	10.3
10°-20°	454.7	28.1
20°-30°	500.8	31.0
30°-40°	191.3	11.8
40°-50°	90.3	5.6
50°-60°	89.8	5.6
60°-70°	71.9	4.4
70°-80°	41.3	2.6
80°-90°	11.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1121.3	69.3
0°-40°	1312.6	81.2
0°-60°	1492.7	92.3
0°-90°	1617.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1617.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1818	
5°	1758	166
15°	1635	455
25°	1076	501
35°	244	191
45°	118	90
55°	101	90
65°	73	72
75°	39	41
85°	10	11
90°	0	



TEST NUMBER: P746613

CATALOG NUMBER: LD4D30D010-EU4DR7020359027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1818.2
2.5°	1799.2
5°	1757.5
7.5°	1722.6
10°	1688.9
12.5°	1660.5
15°	1634.9
17.5°	1573.0
20°	1485.1
22.5°	1295.7
25°	1076.1
27.5°	936.8
30°	726.9
32.5°	469.5
35°	243.6
37.5°	131.5
40°	119.7
42.5°	118.9
45°	117.7
47.5°	115.2
50°	110.8
52.5°	105.9
55°	100.8
57.5°	95.0
60°	88.4
62.5°	80.9
65°	73.1
67.5°	64.5
70°	55.9
72.5°	47.2
75°	39.1
77.5°	30.8
80°	23.3
82.5°	16.4
85°	9.5
87.5°	3.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)