

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745835

Luminaire Tested: LD4D30D010-EU4DR2015309030-4LBCSSQMB

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR2015309030-4LBCSSQMB  
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2652.3 lumens  
Efficiency: N/A  
Efficacy: 91.5 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745835  
CATALOG NUMBER: LD4D30D010-EU4DR2015309030-4LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P745835  
 CATALOG NUMBER: LD4D30D010-EU4DR2015309030-4LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75				
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75								
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	90	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75											
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	87	86	85	84	83	82	81	80	79	78	77	76	75														
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	84	83	82	81	80	79	78	77	76	75																	
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	82	81	80	79	78	77	76	75																			
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79	78	77	76	75																					
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77	76	75																							
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	76	75																									
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1649477
5°	1488135
10°	835226
15°	424555
20°	179758
25°	82979
30°	43930
35°	23675
40°	12651
45°	7479
50°	4334
55°	2305
60°	1464
65°	1034
70°	415
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7479 cd/sqm



TEST NUMBER: P745835

CATALOG NUMBER: LD4D30D010-EU4DR2015309030-4LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1074.9	40.5
10°-20°	1058.4	39.9
20°-30°	345.8	13.0
30°-40°	117.7	4.4
40°-50°	39.6	1.5
50°-60°	11.9	0.4
60°-70°	4.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2479.0	93.5
0°-40°	2596.8	97.9
0°-60°	2648.2	99.8
0°-90°	2652.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2652.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15097	
5°	13568	###
15°	3753	1058
25°	688	346
35°	178	118
45°	48	40
55°	12	12
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745835

CATALOG NUMBER: LD4D30D010-EU4DR2015309030-4LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	15096.7
0.5°	15096.7
1°	15077.9
1.5°	15040.3
2°	14971.7
2.5°	14880.3
3°	14751.2
3.5°	14571.1
4°	14303.6
4.5°	13978.3
5°	13568.2
5.5°	13029.2
6°	12476.7
6.5°	11843.5
7°	11223.7
7.5°	10497.8
8°	9849.9
8.5°	9197.9
9°	8595.6
9.5°	8043.1
10°	7528.2
12.5°	5405.5
15°	3753.3
17.5°	2452.0
20°	1546.0
22.5°	1001.5
25°	688.3
27.5°	484.0
30°	348.2
32.5°	250.0
35°	177.5
37.5°	123.7
40°	88.7
42.5°	64.5
45°	48.4
47.5°	37.6
50°	25.5
52.5°	16.1
55°	12.1
57.5°	9.4
60°	6.7
62.5°	5.4
65°	4.0



TEST NUMBER: P745835  
CATALOG NUMBER: LD4D30D010-EU4DR2015309030-4LBCSSQMB

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		2.7
70°		1.3

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)