

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739744

Luminaire Tested: LD4D02D010-EU4DR700210IC9050-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P739744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR700210IC9050-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 371.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739744

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9050-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P739744

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9050-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97	97	95	94	93	93	93	93																
	1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93	93	93	93	93	93	93	93	93	93																
	2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85	85	85	85	85	85	85	85																
	3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	78	78	78	78	78	78	78	78	78																
	4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71	71	71	71	71	71	71	71	71	71																
	5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	65	65	65	65	65	65	65	65	65																
	6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60	60	60	60	60	60	60	60	60	60																
	7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56	56	56	56	56	56	56	56	56	56																
	8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51	51	51	51	51	51	51	51																
	9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48	48	48	48	48	48	48	48	48	48																
	10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44	44	44	44	44	44	44	44	44	44																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31992
5°	31905
10°	31842
15°	31831
20°	31522
25°	29609
30°	26393
35°	21048
40°	13978
45°	8359
50°	4334
55°	2286
60°	809
65°	26
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8359 cd/sqm



TEST NUMBER: P739744

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9050-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.7	7.5
10°-20°	79.4	21.4
20°-30°	111.9	30.2
30°-40°	96.6	26.1
40°-50°	43.3	11.7
50°-60°	11.3	3.1
60°-70°	0.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	219.0	59.0
0°-40°	315.6	85.1
0°-60°	370.2	99.8
0°-90°	371.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	371.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	293	
5°	291	28
15°	281	79
25°	246	112
35°	158	97
45°	54	43
55°	12	11
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P739744

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9050-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	292.8
2.5°	292.5
5°	290.9
7.5°	289.7
10°	287.0
12.5°	284.6
15°	281.4
17.5°	277.8
20°	271.1
22.5°	260.1
25°	245.6
27.5°	228.8
30°	209.2
32.5°	185.3
35°	157.8
37.5°	127.5
40°	98.0
42.5°	74.4
45°	54.1
47.5°	37.3
50°	25.5
52.5°	17.6
55°	12.0
57.5°	7.2
60°	3.7
62.5°	1.1
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)