

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745508

Luminaire Tested: LD4D25D010-EU4DR6020359024-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P745508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR6020359024-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1663.6 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745508

CATALOG NUMBER: LD4D25D010-EU4DR6020359024-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P745508

CATALOG NUMBER: LD4D25D010-EU4DR6020359024-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215866
5°	221177
10°	223845
15°	213245
20°	188013
25°	152069
30°	102861
35°	51552
40°	8358
45°	8174
50°	8346
55°	8477
60°	8719
65°	8894
70°	9105
75°	9203
80°	8935
85°	7396

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 9203 cd/sqm



TEST NUMBER: P745508

CATALOG NUMBER: LD4D25D010-EU4DR6020359024-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.7	11.6
10°-20°	521.4	31.3
20°-30°	561.0	33.7
30°-40°	243.9	14.7
40°-50°	41.0	2.5
50°-60°	39.8	2.4
60°-70°	34.0	2.0
70°-80°	22.8	1.4
80°-90°	6.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1275.2	76.7
0°-40°	1519.1	91.3
0°-60°	1599.9	96.2
0°-90°	1663.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1663.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1976	
5°	2017	193
15°	1885	521
25°	1261	561
35°	386	244
45°	53	41
55°	44	40
65°	34	34
75°	22	23
85°	6	7
90°	0	



TEST NUMBER: P745508

CATALOG NUMBER: LD4D25D010-EU4DR6020359024-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1975.7
2.5°	2031.2
5°	2016.6
7.5°	2021.2
10°	2017.6
12.5°	1975.9
15°	1885.2
17.5°	1763.3
20°	1617.0
22.5°	1460.4
25°	1261.4
27.5°	1008.9
30°	815.3
32.5°	628.4
35°	386.5
37.5°	165.4
40°	58.6
42.5°	54.0
45°	52.9
47.5°	51.2
50°	49.1
52.5°	46.8
55°	44.5
57.5°	42.2
60°	39.9
62.5°	37.3
65°	34.4
67.5°	31.6
70°	28.5
72.5°	25.2
75°	21.8
77.5°	18.0
80°	14.2
82.5°	10.0
85°	5.9
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)