

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746250

Luminaire Tested: LD4D30D010-EU4DR4520359035-4LBSQW1MW

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746250  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR4520359035-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 45° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2662.5 lumens  
Efficiency: N/A  
Efficacy: 91.8 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P746250  
CATALOG NUMBER: LD4D30D010-EU4DR4520359035-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P746250

CATALOG NUMBER: LD4D30D010-EU4DR4520359035-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98	98	97	95
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91	89	87	85
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87	84	82	81
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74	73
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77	73	71	69
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73	70	67	66
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71	67	64	63
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68	64	61	60

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	514192
5°	499551
10°	477934
15°	437416
20°	347016
25°	216651
30°	119414
35°	53620
40°	21123
45°	9951
50°	4725
55°	2457
60°	1224
65°	284
70°	96
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9951 cd/sqm



TEST NUMBER: P746250

CATALOG NUMBER: LD4D30D010-EU4DR4520359035-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	428.0	16.1
10°-20°	1053.3	39.6
20°-30°	834.1	31.3
30°-40°	277.8	10.4
40°-50°	55.1	2.1
50°-60°	12.5	0.5
60°-70°	1.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2315.3	87.0
0°-40°	2593.0	97.4
0°-60°	2660.7	99.9
0°-90°	2662.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2662.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4706	
5°	4555	428
15°	3867	1053
25°	1797	834
35°	402	278
45°	64	55
55°	13	13
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746250

CATALOG NUMBER: LD4D30D010-EU4DR4520359035-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4706.1
2.5°	4675.3
5°	4554.7
7.5°	4455.1
10°	4307.8
12.5°	4111.6
15°	3867.0
17.5°	3499.0
20°	2984.5
22.5°	2371.6
25°	1797.1
27.5°	1315.9
30°	946.5
32.5°	643.7
35°	402.0
37.5°	238.3
40°	148.1
42.5°	97.3
45°	64.4
47.5°	41.5
50°	27.8
52.5°	18.5
55°	12.9
57.5°	8.5
60°	5.6
62.5°	3.0
65°	1.1
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)