

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746552

Luminaire Tested: LD4D30D010-EU4DR6520359035-4LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746552  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR6520359035-4LBCSSQMW  
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2534.3 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P746552  
CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P746552  
 CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	134393
5°	134056
10°	133940
15°	129810
20°	118176
25°	102984
30°	85654
35°	67869
40°	48985
45°	30949
50°	16137
55°	8574
60°	4509
65°	2474
70°	1042
75°	1151
80°	774
85°	670

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 30949 cd/sqm



TEST NUMBER: P746552  
 CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	217.6	8.6
10°-20°	595.9	23.5
20°-30°	728.4	28.7
30°-40°	591.0	23.3
40°-50°	294.5	11.6
50°-60°	82.2	3.2
60°-70°	18.7	0.7
70°-80°	4.9	0.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1541.9	60.8
0°-40°	2132.9	84.2
0°-60°	2509.6	99.0
0°-90°	2534.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2534.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2301	
5°	2287	218
15°	2147	596
25°	1598	728
35°	952	591
45°	375	295
55°	84	82
65°	18	19
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P746552

CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2301.1
2.5°	2299.4
5°	2286.6
7.5°	2279.1
10°	2258.5
12.5°	2216.6
15°	2146.9
17.5°	2038.0
20°	1901.4
22.5°	1754.0
25°	1598.1
27.5°	1431.4
30°	1270.1
32.5°	1110.8
35°	951.9
37.5°	793.3
40°	642.5
42.5°	501.2
45°	374.7
47.5°	261.0
50°	177.6
52.5°	122.4
55°	84.2
57.5°	56.8
60°	38.6
62.5°	26.7
65°	17.9
67.5°	9.1
70°	6.1
72.5°	5.7
75°	5.1
77.5°	3.4
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)