

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745794

Luminaire Tested: LD4D30D010-EU4DR1515309040-4LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745794
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR1515309040-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2536.3 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745794

CATALOG NUMBER: LD4D30D010-EU4DR1515309040-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P745794

CATALOG NUMBER: LD4D30D010-EU4DR1515309040-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3888217	3888217	3888217
5°	2284902	2255308	2273154
10°	681939	686716	697222
15°	169623	172932	167590
20°	50755	58773	51827
25°	17894	22794	18120
30°	6575	8656	6679
35°	3290	3718	3188
40°	2081	2287	2081
45°	1533	1638	1533
50°	1224	1224	1224
55°	1016	1016	1016
60°	821	821	821
65°	628	628	628
70°	534	534	534
75°	333	333	446
80°	229	229	229
85°	125	125	125

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1638 cd/sqm



TEST NUMBER: P745794

CATALOG NUMBER: LD4D30D010-EU4DR1515309040-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1644.9	64.9
10°-20°	676.6	26.7
20°-30°	134.4	5.3
30°-40°	33.5	1.3
40°-50°	17.6	0.7
50°-60°	13.1	0.5
60°-70°	9.2	0.4
70°-80°	5.3	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2455.9	96.8
0°-40°	2489.5	98.2
0°-60°	2520.2	99.4
0°-90°	2536.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2536.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	34556	34556	34556	34556	34556	
5°	22483	22252	22192	22345	22367	1642
15°	1953	1990	1991	1956	1930	670
25°	230	260	293	259	233	121
35°	45	48	51	48	44	31
45°	22	22	23	22	22	17
55°	15	15	15	15	15	13
65°	9	9	9	9	9	9
75°	4	4	4	4	6	5
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P745794

CATALOG NUMBER: LD4D30D010-EU4DR1515309040-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	34555.8	34555.8	34555.8	34555.8	34555.8
2.5°	31170.7	31197.0	31207.3	31238.0	31352.1
5°	22482.8	22251.6	22191.6	22345.2	22367.2
7.5°	13317.9	13364.7	13535.9	13573.9	13436.4
10°	7308.5	7368.4	7359.7	7412.3	7472.3
12.5°	3737.6	3690.8	3676.2	3736.2	3652.8
15°	1952.9	1989.5	1991.0	1955.8	1929.5
17.5°	1050.3	1092.8	1163.0	1105.9	1018.2
20°	620.3	658.3	718.3	671.5	633.4
22.5°	383.3	414.0	456.4	419.8	389.1
25°	229.7	260.4	292.6	258.9	232.6
27.5°	136.0	162.4	182.9	160.9	134.6
30°	87.8	102.4	115.6	100.9	89.2
32.5°	61.4	67.3	73.1	67.3	61.4
35°	45.3	48.3	51.2	48.3	43.9
37.5°	35.1	38.0	39.5	36.6	33.6
40°	29.3	30.7	32.2	30.7	29.3
42.5°	24.9	26.3	26.3	26.3	24.9
45°	21.9	21.9	23.4	21.9	21.9
47.5°	19.0	19.0	20.5	19.0	19.0
50°	17.6	17.6	17.6	17.6	17.6
52.5°	16.1	16.1	16.1	16.1	16.1
55°	14.6	14.6	14.6	14.6	14.6
57.5°	13.2	13.2	13.2	13.2	13.2
60°	11.7	11.7	11.7	11.7	11.7
62.5°	10.2	10.2	10.2	10.2	10.2
65°	8.8	8.8	8.8	8.8	8.8
67.5°	8.8	8.8	8.8	8.8	8.8
70°	7.3	7.3	7.3	7.3	7.3
72.5°	5.9	5.9	5.9	5.9	5.9
75°	4.4	4.4	4.4	4.4	5.9
77.5°	4.4	4.4	4.4	4.4	4.4
80°	2.9	2.9	2.9	2.9	2.9
82.5°	2.9	2.9	2.9	2.9	2.9
85°	1.5	1.5	1.5	1.5	1.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)