

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745862

Luminaire Tested: LD4D30D010-EU4DR2015309040-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR2015309040-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2877.5 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745862

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P745862

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	96	95	94															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92	91	91															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	89	88	85	85															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	86	85	83	83															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	84	83	81	81															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	82	81	79	79															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79	77	77															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77	75	75															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	76	75	73	73															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	74	73	71	71															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1789462
5°	1614429
10°	906109
15°	460593
20°	195013
25°	90019
30°	47652
35°	25676
40°	13735
45°	8112
50°	4708
55°	2495
60°	1595
65°	1138
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8112 cd/sqm



TEST NUMBER: P745862

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1166.1	40.5
10°-20°	1148.2	39.9
20°-30°	375.1	13.0
30°-40°	127.7	4.4
40°-50°	42.9	1.5
50°-60°	12.9	0.4
60°-70°	4.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2689.4	93.5
0°-40°	2817.1	97.9
0°-60°	2873.0	99.8
0°-90°	2877.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2877.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16378	
5°	14720	###
15°	4072	1148
25°	747	375
35°	192	128
45°	52	43
55°	13	13
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745862

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	16377.9
0.5°	16377.9
1°	16357.5
1.5°	16316.7
2°	16242.3
2.5°	16143.1
3°	16003.1
3.5°	15807.7
4°	15517.5
4.5°	15164.5
5°	14719.7
5.5°	14134.9
6°	13535.5
6.5°	12848.6
7°	12176.2
7.5°	11388.7
8°	10685.8
8.5°	9978.4
9°	9325.1
9.5°	8725.7
10°	8167.1
12.5°	5864.3
15°	4071.9
17.5°	2660.1
20°	1677.2
22.5°	1086.5
25°	746.7
27.5°	525.0
30°	377.7
32.5°	271.3
35°	192.5
37.5°	134.2
40°	96.3
42.5°	70.0
45°	52.5
47.5°	40.8
50°	27.7
52.5°	17.5
55°	13.1
57.5°	10.2
60°	7.3
62.5°	5.8
65°	4.4



TEST NUMBER: P745862

CATALOG NUMBER: LD4D30D010-EU4DR2015309040-4LBCSSQMMS

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		2.9
70°		1.5

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)