

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746643

Luminaire Tested: LD4D30D010-EU4DR7020359040-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P746643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR7020359040-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2913.1 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746643

CATALOG NUMBER: LD4D30D010-EU4DR7020359040-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P746643

CATALOG NUMBER: LD4D30D010-EU4DR7020359040-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																											
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																											
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78																											
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71																											
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65																											
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60																											
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56																											
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51																											
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48																											
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	251223
5°	250593
10°	250051
15°	249984
20°	247545
25°	232528
30°	207299
35°	165288
40°	109754
45°	65608
50°	34013
55°	17868
60°	6315
65°	103
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 65608 cd/sqm



TEST NUMBER: P746643

CATALOG NUMBER: LD4D30D010-EU4DR7020359040-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.3	7.5
10°-20°	623.2	21.4
20°-30°	879.1	30.2
30°-40°	758.9	26.1
40°-50°	339.8	11.7
50°-60°	89.0	3.1
60°-70°	5.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1719.6	59.0
0°-40°	2478.5	85.1
0°-60°	2907.3	99.8
0°-90°	2913.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2913.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2299	
5°	2285	217
15°	2210	623
25°	1929	879
35°	1239	759
45°	425	340
55°	94	89
65°	0	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746643

CATALOG NUMBER: LD4D30D010-EU4DR7020359040-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2299.3
2.5°	2296.8
5°	2284.8
7.5°	2274.9
10°	2253.8
12.5°	2234.8
15°	2210.0
17.5°	2181.5
20°	2129.0
22.5°	2042.5
25°	1928.8
27.5°	1796.9
30°	1643.1
32.5°	1455.0
35°	1239.2
37.5°	1001.0
40°	769.5
42.5°	584.6
45°	424.6
47.5°	292.7
50°	200.1
52.5°	138.1
55°	93.8
57.5°	56.7
60°	28.9
62.5°	9.1
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)