

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745069

Luminaire Tested: LD4D25D010-EU4DR3020359035-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P745069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR3020359035-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2243.1 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745069

CATALOG NUMBER: LD4D25D010-EU4DR3020359035-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P745069

CATALOG NUMBER: LD4D25D010-EU4DR3020359035-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	552100	552100	552100
5°	536252	535622	536275
10°	464472	461200	464363
15°	303043	301419	299905
20°	150693	156346	150490
25°	75909	85596	74347
30°	30395	33118	26480
35°	14100	13502	11316
40°	6085	6765	5735
45°	4287	5326	4330
50°	1477	3882	1560
55°	854	1601	894
60°	597	704	597
65°	380	380	380
70°	246	157	246
75°	0	89	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 5326 cd/sqm



TEST NUMBER: P745069

CATALOG NUMBER: LD4D25D010-EU4DR3020359035-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	634.3	28.3
10°-20°	1021.5	45.5
20°-30°	441.4	19.7
30°-40°	100.6	4.5
40°-50°	34.5	1.5
50°-60°	8.4	0.4
60°-70°	2.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2097.2	93.5
0°-40°	2197.8	98.0
0°-60°	2240.8	99.9
0°-90°	2243.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2243.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	7213	7213	7213	7213	7213	
5°	6979	6972	6971	6986	6980	635
15°	3824	3778	3804	3791	3785	1024
25°	899	933	1014	909	880	430
35°	151	154	144	143	121	102
45°	40	49	49	49	40	28
55°	6	7	12	7	7	6
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P745069

CATALOG NUMBER: LD4D25D010-EU4DR3020359035-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	7212.9	7212.9	7212.9	7212.9	7212.9
2.5°	7165.1	7160.2	7163.0	7166.5	7168.0
5°	6979.2	6972.5	6971.0	6985.5	6979.5
7.5°	6604.2	6594.6	6580.1	6613.0	6643.8
10°	5975.9	5965.3	5933.8	5949.3	5974.5
12.5°	5048.4	5014.1	5013.4	5063.0	5056.2
15°	3824.2	3778.2	3803.7	3791.3	3784.6
17.5°	2571.7	2554.0	2588.0	2577.7	2533.4
20°	1850.0	1854.6	1919.4	1886.8	1847.5
22.5°	1349.9	1366.6	1443.4	1359.5	1328.7
25°	898.8	932.8	1013.5	909.0	880.3
27.5°	552.8	568.4	650.2	545.7	530.2
30°	343.9	336.1	374.7	321.5	299.6
32.5°	225.6	215.7	228.0	204.7	187.0
35°	150.9	154.1	144.5	143.4	121.1
37.5°	94.2	108.3	95.6	102.0	77.9
40°	60.9	78.6	67.7	74.7	57.4
42.5°	49.9	60.6	55.6	59.1	51.0
45°	39.6	49.2	49.2	49.2	40.0
47.5°	21.9	32.9	42.2	33.6	23.4
50°	12.4	16.6	32.6	17.4	13.1
52.5°	8.5	9.6	22.3	9.9	8.9
55°	6.4	6.7	12.0	7.1	6.7
57.5°	5.0	5.3	6.4	5.3	5.0
60°	3.9	3.9	4.6	4.2	3.9
62.5°	2.8	2.8	3.2	2.8	2.8
65°	2.1	2.1	2.1	2.1	2.1
67.5°	1.1	1.4	1.4	1.4	1.4
70°	1.1	0.7	0.7	0.7	1.1
72.5°	0.7	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)