

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745876

Luminaire Tested: LD4D30D010-EU4DR2015309050-4LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745876  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR2015309050-4LBCSSQMW  
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2843.6 lumens  
Efficiency: N/A  
Efficacy: 98.1 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745876

CATALOG NUMBER: LD4D30D010-EU4DR2015309050-4LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P745876

CATALOG NUMBER: LD4D30D010-EU4DR2015309050-4LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |    |     |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |   |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |    |     |  |  |  |  |  | 10 |  |  |  |  |  |  |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |     |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    | 100 |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 97 | 98 | 98 | 97  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 104 | 101 | 103 | 101 | 99  | 100 | 99  | 97  | 98  | 96  | 95  | 94  | 94 | 98 | 96 | 95  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 100 | 97  | 95  | 97  | 95  | 93  | 95  | 93  | 92  | 91  | 91 | 98 | 93 | 92  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 4   | 105 | 99  | 96  | 93  | 103 | 98  | 95  | 92  | 96  | 93  | 91  | 95  | 92  | 90  | 93  | 91  | 89  | 88  | 88 | 93 | 91 | 89  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 5   | 102 | 96  | 92  | 89  | 100 | 95  | 91  | 89  | 94  | 90  | 88  | 92  | 89  | 87  | 91  | 88  | 86  | 85  | 85 | 91 | 88 | 86  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 6   | 99  | 93  | 89  | 86  | 98  | 92  | 88  | 86  | 91  | 87  | 85  | 90  | 87  | 84  | 88  | 86  | 84  | 83  | 83 | 88 | 86 | 84  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 7   | 96  | 90  | 86  | 83  | 95  | 89  | 86  | 83  | 88  | 85  | 82  | 87  | 84  | 82  | 86  | 84  | 82  | 81  | 81 | 86 | 84 | 82  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 8   | 94  | 87  | 83  | 81  | 93  | 87  | 83  | 80  | 86  | 83  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 79  | 79 | 84 | 82 | 80  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 9   | 91  | 85  | 81  | 78  | 91  | 85  | 81  | 78  | 84  | 80  | 78  | 83  | 80  | 78  | 82  | 80  | 78  | 77  | 77 | 82 | 80 | 78  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |
| 10  | 89  | 83  | 79  | 76  | 88  | 82  | 79  | 76  | 82  | 78  | 76  | 81  | 78  | 76  | 81  | 78  | 76  | 75  | 75 | 81 | 78 | 76  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°      |
|-----|---------|
| 0°  | 1768363 |
| 5°  | 1595389 |
| 10° | 895425  |
| 15° | 455164  |
| 20° | 192711  |
| 25° | 88958   |
| 30° | 47097   |
| 35° | 25369   |
| 40° | 13564   |
| 45° | 8019    |
| 50° | 4657    |
| 55° | 2476    |
| 60° | 1573    |
| 65° | 1112    |
| 70° | 447     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8019 cd/sqm



TEST NUMBER: P745876

CATALOG NUMBER: LD4D30D010-EU4DR2015309050-4LBCSSQMW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1152.3 | 40.5      |
| 10°-20°   | 1134.7 | 39.9      |
| 20°-30°   | 370.7  | 13.0      |
| 30°-40°   | 126.2  | 4.4       |
| 40°-50°   | 42.5   | 1.5       |
| 50°-60°   | 12.8   | 0.4       |
| 60°-70°   | 4.3    | 0.1       |
| 70°-80°   | 0.2    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2657.7 | 93.5      |
| 0°-40°    | 2783.9 | 97.9      |
| 0°-60°    | 2839.1 | 99.8      |
| 0°-90°    | 2843.6 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2843.6 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 16185 |      |
| 5°  | 14546 | ###  |
| 15° | 4024  | 1135 |
| 25° | 738   | 371  |
| 35° | 190   | 126  |
| 45° | 52    | 42   |
| 55° | 13    | 13   |
| 65° | 4     | 4    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P745876

CATALOG NUMBER: LD4D30D010-EU4DR2015309050-4LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 16184.8 |
| 0.5°  | 16184.8 |
| 1°    | 16164.6 |
| 1.5°  | 16124.3 |
| 2°    | 16050.8 |
| 2.5°  | 15952.8 |
| 3°    | 15814.4 |
| 3.5°  | 15621.3 |
| 4°    | 15334.5 |
| 4.5°  | 14985.7 |
| 5°    | 14546.1 |
| 5.5°  | 13968.2 |
| 6°    | 13375.9 |
| 6.5°  | 12697.1 |
| 7°    | 12032.7 |
| 7.5°  | 11254.4 |
| 8°    | 10559.7 |
| 8.5°  | 9860.8  |
| 9°    | 9215.1  |
| 9.5°  | 8622.8  |
| 10°   | 8070.8  |
| 12.5° | 5795.1  |
| 15°   | 4023.9  |
| 17.5° | 2628.8  |
| 20°   | 1657.4  |
| 22.5° | 1073.7  |
| 25°   | 737.9   |
| 27.5° | 518.8   |
| 30°   | 373.3   |
| 32.5° | 268.1   |
| 35°   | 190.2   |
| 37.5° | 132.6   |
| 40°   | 95.1    |
| 42.5° | 69.2    |
| 45°   | 51.9    |
| 47.5° | 40.4    |
| 50°   | 27.4    |
| 52.5° | 17.3    |
| 55°   | 13.0    |
| 57.5° | 10.1    |
| 60°   | 7.2     |
| 62.5° | 5.8     |
| 65°   | 4.3     |



TEST NUMBER: P745876  
CATALOG NUMBER: LD4D30D010-EU4DR2015309050-4LBCSSQMW

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



|       |  |     |
|-------|--|-----|
| 67.5° |  | 2.9 |
| 70°   |  | 1.4 |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)