

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746665

Luminaire Tested: LD4D30D010-EU4DR7020359050-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746665  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR7020359050-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1790.3 lumens  
Efficiency: N/A  
Efficacy: 61.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P746665

CATALOG NUMBER: LD4D30D010-EU4DR7020359050-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P746665

CATALOG NUMBER: LD4D30D010-EU4DR7020359050-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	219909
5°	213379
10°	207436
15°	204704
20°	191153
25°	143606
30°	101524
35°	35960
40°	18913
45°	20134
50°	20856
55°	21259
60°	21393
65°	20941
70°	19742
75°	18279
80°	16234
85°	13163

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 60°  
 Luminance: 21393 cd/sqm



TEST NUMBER: P746665

CATALOG NUMBER: LD4D30D010-EU4DR7020359050-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.5	10.3
10°-20°	503.3	28.1
20°-30°	554.4	31.0
30°-40°	211.8	11.8
40°-50°	100.0	5.6
50°-60°	99.4	5.6
60°-70°	79.6	4.4
70°-80°	45.7	2.6
80°-90°	12.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1241.2	69.3
0°-40°	1453.0	81.2
0°-60°	1652.5	92.3
0°-90°	1790.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1790.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2013	
5°	1946	184
15°	1810	503
25°	1191	554
35°	270	212
45°	130	100
55°	112	99
65°	81	80
75°	43	46
85°	10	12
90°	0	



TEST NUMBER: P746665

CATALOG NUMBER: LD4D30D010-EU4DR7020359050-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2012.7
2.5°	1991.7
5°	1945.5
7.5°	1907.0
10°	1869.7
12.5°	1838.1
15°	1809.7
17.5°	1741.2
20°	1644.0
22.5°	1434.3
25°	1191.2
27.5°	1037.0
30°	804.7
32.5°	519.8
35°	269.6
37.5°	145.6
40°	132.6
42.5°	131.6
45°	130.3
47.5°	127.5
50°	122.7
52.5°	117.3
55°	111.6
57.5°	105.1
60°	97.9
62.5°	89.6
65°	81.0
67.5°	71.4
70°	61.8
72.5°	52.3
75°	43.3
77.5°	34.1
80°	25.8
82.5°	18.2
85°	10.5
87.5°	4.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)