

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747393

Luminaire Tested: LD4D35BD010-EU4DR7020359027-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P747393
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR7020359027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1934.0 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747393
CATALOG NUMBER: LD4D35BD010-EU4DR7020359027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P747393

CATALOG NUMBER: LD4D35BD010-EU4DR7020359027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	237588
5°	230521
10°	224100
15°	221163
20°	206512
25°	155143
30°	109674
35°	38854
40°	20425
45°	21756
50°	22522
55°	22954
60°	23098
65°	22596
70°	21340
75°	19757
80°	17555
85°	14291

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 23101 cd/sqm



TEST NUMBER: P747393

CATALOG NUMBER: LD4D35BD010-EU4DR7020359027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.2	10.3
10°-20°	543.8	28.1
20°-30°	598.9	31.0
30°-40°	228.8	11.8
40°-50°	108.0	5.6
50°-60°	107.4	5.6
60°-70°	86.0	4.4
70°-80°	49.4	2.6
80°-90°	13.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1340.9	69.3
0°-40°	1569.7	81.2
0°-60°	1785.2	92.3
0°-90°	1934.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1934.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2174	
5°	2102	198
15°	1955	544
25°	1287	599
35°	291	229
45°	141	108
55°	120	107
65°	87	86
75°	47	49
85°	11	13
90°	0	



TEST NUMBER: P747393

CATALOG NUMBER: LD4D35BD010-EU4DR7020359027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2174.5
2.5°	2151.7
5°	2101.8
7.5°	2060.2
10°	2019.9
12.5°	1985.8
15°	1955.2
17.5°	1881.1
20°	1776.1
22.5°	1549.6
25°	1286.9
27.5°	1120.3
30°	869.3
32.5°	561.5
35°	291.3
37.5°	157.3
40°	143.2
42.5°	142.2
45°	140.8
47.5°	137.7
50°	132.5
52.5°	126.7
55°	120.5
57.5°	113.6
60°	105.7
62.5°	96.7
65°	87.4
67.5°	77.1
70°	66.8
72.5°	56.5
75°	46.8
77.5°	36.8
80°	27.9
82.5°	19.6
85°	11.4
87.5°	4.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)