

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746850

Luminaire Tested: LD4D35BD010-EU4DR3520359030-4LBCSSQMMS

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746850  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR3520359030-4LBCSSQMMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2937.2 lumens  
Efficiency: N/A  
Efficacy: 95.4 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P746850  
CATALOG NUMBER: LD4D35BD010-EU4DR3520359030-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P746850

CATALOG NUMBER: LD4D35BD010-EU4DR3520359030-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	98	96	96	96	92	92	92																
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	96	92	91	91	89	89	89	84	84	84																
	2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	92	88	87	87	85	85	85	81	81	81																
	3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88	88	88	84	83	83	82	82	82	78	78	78																
	4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84	84	84	80	79	79	77	77	77	73	73	73																
	5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81	81	81	78	77	77	76	76	76	72	72	72																
	6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78	78	78	75	74	74	73	73	73	69	69	69																
	7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75	75	75	72	71	71	70	70	70	66	66	66																
	8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72	72	72	69	68	68	67	67	67	63	63	63																
	9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70	70	70	67	66	66	65	65	65	61	61	61																
	10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68	68	68	65	64	64	63	63	63	59	59	59																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	883013
5°	862267
10°	777123
15°	603175
20°	342110
25°	133094
30°	49658
35°	27223
40°	17786
45°	10832
50°	6884
55°	4877
60°	3562
65°	1939
70°	128
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10832 cd/sqm



TEST NUMBER: P746850

CATALOG NUMBER: LD4D35BD010-EU4DR3520359030-4LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	723.0	24.6
10°-20°	1411.7	48.1
20°-30°	575.7	19.6
30°-40°	137.8	4.7
40°-50°	57.4	2.0
50°-60°	23.8	0.8
60°-70°	7.4	0.3
70°-80°	0.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2710.5	92.3
0°-40°	2848.3	97.0
0°-60°	2929.5	99.7
0°-90°	2937.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2937.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8082	
5°	7862	723
15°	5332	1412
25°	1104	576
35°	204	138
45°	70	57
55°	26	24
65°	8	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746850

CATALOG NUMBER: LD4D35BD010-EU4DR3520359030-4LBCSSQMMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8081.7
2.5°	8033.2
5°	7861.8
7.5°	7519.7
10°	7004.5
12.5°	6279.1
15°	5332.4
17.5°	4174.6
20°	2942.3
22.5°	1876.2
25°	1104.0
27.5°	624.1
30°	393.6
32.5°	276.3
35°	204.1
37.5°	157.8
40°	124.7
42.5°	96.1
45°	70.1
47.5°	52.4
50°	40.5
52.5°	32.2
55°	25.6
57.5°	20.7
60°	16.3
62.5°	11.9
65°	7.5
67.5°	2.6
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)