

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747251

Luminaire Tested: LD4D35BD010-EU4DR6020359030-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P747251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6020359030-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2880.7 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747251

CATALOG NUMBER: LD4D35BD010-EU4DR6020359030-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P747251

CATALOG NUMBER: LD4D35BD010-EU4DR6020359030-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	373803
5°	382996
10°	387613
15°	369264
20°	325576
25°	263330
30°	178118
35°	89260
40°	14477
45°	14169
50°	14448
55°	14668
60°	15078
65°	15434
70°	15781
75°	15957
80°	15416
85°	12787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 15957 cd/sqm



TEST NUMBER: P747251

CATALOG NUMBER: LD4D35BD010-EU4DR6020359030-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.7	11.6
10°-20°	903.0	31.3
20°-30°	971.5	33.7
30°-40°	422.3	14.7
40°-50°	70.9	2.5
50°-60°	68.9	2.4
60°-70°	59.0	2.0
70°-80°	39.5	1.4
80°-90°	11.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2208.2	76.7
0°-40°	2630.5	91.3
0°-60°	2770.4	96.2
0°-90°	2880.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2880.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3421	
5°	3492	334
15°	3264	903
25°	2184	972
35°	669	422
45°	92	71
55°	77	69
65°	60	59
75°	38	39
85°	10	12
90°	0	



TEST NUMBER: P747251

CATALOG NUMBER: LD4D35BD010-EU4DR6020359030-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3421.2
2.5°	3517.3
5°	3492.0
7.5°	3500.0
10°	3493.7
12.5°	3421.6
15°	3264.5
17.5°	3053.4
20°	2800.1
22.5°	2528.9
25°	2184.3
27.5°	1747.1
30°	1411.8
32.5°	1088.2
35°	669.2
37.5°	286.3
40°	101.5
42.5°	93.5
45°	91.7
47.5°	88.6
50°	85.0
52.5°	81.0
55°	77.0
57.5°	73.0
60°	69.0
62.5°	64.6
65°	59.7
67.5°	54.8
70°	49.4
72.5°	43.6
75°	37.8
77.5°	31.2
80°	24.5
82.5°	17.4
85°	10.2
87.5°	3.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)