

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747329

Luminaire Tested: LD4D35BD010-EU4DR6520359030-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P747329  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR6520359030-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2519.2 lumens  
Efficiency: N/A  
Efficacy: 81.8 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P747329  
CATALOG NUMBER: LD4D35BD010-EU4DR6520359030-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P747329

CATALOG NUMBER: LD4D35BD010-EU4DR6520359030-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	270999
5°	271223
10°	280772
15°	281238
20°	258916
25°	220617
30°	168882
35°	119311
40°	70431
45°	28586
50°	10369
55°	5772
60°	3322
65°	1810
70°	1917
75°	1478
80°	1573
85°	1379

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 28586 cd/sqm



TEST NUMBER: P747329

CATALOG NUMBER: LD4D35BD010-EU4DR6520359030-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	238.8	9.5
10°-20°	688.9	27.3
20°-30°	826.6	32.8
30°-40°	555.5	22.0
40°-50°	166.3	6.6
50°-60°	29.4	1.2
60°-70°	8.3	0.3
70°-80°	4.1	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1754.3	69.6
0°-40°	2309.8	91.7
0°-60°	2505.4	99.5
0°-90°	2519.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2519.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2480	
5°	2473	239
15°	2486	689
25°	1830	827
35°	894	555
45°	185	166
55°	30	29
65°	7	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P747329

CATALOG NUMBER: LD4D35BD010-EU4DR6520359030-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2480.3
2.5°	2490.8
5°	2472.9
7.5°	2510.2
10°	2530.7
12.5°	2525.7
15°	2486.3
17.5°	2389.7
20°	2226.8
22.5°	2035.1
25°	1830.0
27.5°	1598.4
30°	1338.6
32.5°	1103.2
35°	894.5
37.5°	688.4
40°	493.8
42.5°	322.5
45°	185.0
47.5°	98.0
50°	61.0
52.5°	42.3
55°	30.3
57.5°	21.9
60°	15.2
62.5°	9.9
65°	7.0
67.5°	6.3
70°	6.0
72.5°	4.6
75°	3.5
77.5°	3.2
80°	2.5
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)