

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747332

Luminaire Tested: LD4D35BD010-EU4DR6520359035-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P747332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6520359035-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2894.7 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747332

CATALOG NUMBER: LD4D35BD010-EU4DR6520359035-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P747332

CATALOG NUMBER: LD4D35BD010-EU4DR6520359035-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153503
5°	153116
10°	152983
15°	148270
20°	134982
25°	117625
30°	97834
35°	77515
40°	55946
45°	35343
50°	18426
55°	9795
60°	5140
65°	2833
70°	1195
75°	1309
80°	908
85°	804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 35343 cd/sqm



TEST NUMBER: P747332

CATALOG NUMBER: LD4D35BD010-EU4DR6520359035-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.6	8.6
10°-20°	680.6	23.5
20°-30°	832.0	28.7
30°-40°	675.0	23.3
40°-50°	336.4	11.6
50°-60°	93.8	3.2
60°-70°	21.3	0.7
70°-80°	5.6	0.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1761.2	60.8
0°-40°	2436.2	84.2
0°-60°	2866.4	99.0
0°-90°	2894.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2894.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2628	
5°	2612	249
15°	2452	681
25°	1825	832
35°	1087	675
45°	428	336
55°	96	94
65°	20	21
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P747332

CATALOG NUMBER: LD4D35BD010-EU4DR6520359035-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2628.3
2.5°	2626.4
5°	2611.7
7.5°	2603.2
10°	2579.6
12.5°	2531.8
15°	2452.2
17.5°	2327.8
20°	2171.8
22.5°	2003.4
25°	1825.3
27.5°	1634.9
30°	1450.7
32.5°	1268.8
35°	1087.2
37.5°	906.1
40°	733.8
42.5°	572.4
45°	427.9
47.5°	298.2
50°	202.8
52.5°	139.8
55°	96.2
57.5°	64.9
60°	44.0
62.5°	30.5
65°	20.5
67.5°	10.4
70°	7.0
72.5°	6.6
75°	5.8
77.5°	3.9
80°	2.7
82.5°	1.9
85°	1.2
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)