

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746626

Luminaire Tested: LD4D30D010-EU4DR7020359030-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P746626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR7020359030-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1669.9 lumens
Efficiency: N/A
Efficacy: 57.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746626

CATALOG NUMBER: LD4D30D010-EU4DR7020359030-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P746626

CATALOG NUMBER: LD4D30D010-EU4DR7020359030-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205126
5°	199033
10°	193479
15°	190950
20°	178304
25°	133950
30°	94698
35°	33546
40°	17629
45°	18789
50°	19446
55°	19811
60°	19951
65°	19519
70°	18401
75°	17097
80°	15164
85°	12286

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 19951 cd/sqm



TEST NUMBER: P746626

CATALOG NUMBER: LD4D30D010-EU4DR7020359030-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	10.2
10°-20°	469.5	28.1
20°-30°	517.1	31.0
30°-40°	197.6	11.8
40°-50°	93.3	5.6
50°-60°	92.7	5.6
60°-70°	74.2	4.4
70°-80°	42.7	2.6
80°-90°	11.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1157.8	69.3
0°-40°	1355.3	81.2
0°-60°	1541.3	92.3
0°-90°	1669.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1669.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1877	
5°	1815	171
15°	1688	469
25°	1111	517
35°	252	198
45°	122	93
55°	104	93
65°	76	74
75°	40	43
85°	10	12
90°	0	



TEST NUMBER: P746626

CATALOG NUMBER: LD4D30D010-EU4DR7020359030-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1877.4
2.5°	1857.8
5°	1814.7
7.5°	1778.7
10°	1743.9
12.5°	1714.6
15°	1688.1
17.5°	1624.1
20°	1533.5
22.5°	1337.9
25°	1111.1
27.5°	967.3
30°	750.6
32.5°	484.8
35°	251.5
37.5°	135.8
40°	123.6
42.5°	122.8
45°	121.6
47.5°	118.9
50°	114.4
52.5°	109.4
55°	104.0
57.5°	98.1
60°	91.3
62.5°	83.5
65°	75.5
67.5°	66.6
70°	57.6
72.5°	48.8
75°	40.5
77.5°	31.8
80°	24.1
82.5°	17.0
85°	9.8
87.5°	3.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)