

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746966

Luminaire Tested: LD4D35BD010-EU4DR4020359050-4LBCSSQMB

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746966  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR4020359050-4LBCSSQMB  
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3350.8 lumens  
Efficiency: N/A  
Efficacy: 108.8 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P746966  
CATALOG NUMBER: LD4D35BD010-EU4DR4020359050-4LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P746966

CATALOG NUMBER: LD4D35BD010-EU4DR4020359050-4LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96																												
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92																												
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88																												
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84																												
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81																												
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77																												
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74																												
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72																												
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69																												
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	852409
5°	848272
10°	801798
15°	681631
20°	464580
25°	193842
30°	60950
35°	28330
40°	15661
45°	7185
50°	3485
55°	1905
60°	1005
65°	362
70°	160
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7185 cd/sqm



TEST NUMBER: P746966

CATALOG NUMBER: LD4D35BD010-EU4DR4020359050-4LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	722.2	21.6
10°-20°	1617.9	48.3
20°-30°	809.8	24.2
30°-40°	148.5	4.4
40°-50°	41.0	1.2
50°-60°	9.6	0.3
60°-70°	1.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3149.9	94.0
0°-40°	3298.3	98.4
0°-60°	3348.9	99.9
0°-90°	3350.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3350.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7802	
5°	7734	722
15°	6026	1618
25°	1608	810
35°	212	148
45°	46	41
55°	10	10
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746966

CATALOG NUMBER: LD4D35BD010-EU4DR4020359050-4LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7801.6
2.5°	7790.2
5°	7734.2
7.5°	7555.5
10°	7226.9
12.5°	6714.6
15°	6026.0
17.5°	5130.4
20°	3995.6
22.5°	2724.0
25°	1607.9
27.5°	850.0
30°	483.1
32.5°	312.2
35°	212.4
37.5°	151.8
40°	109.8
42.5°	75.2
45°	46.5
47.5°	29.6
50°	20.5
52.5°	14.6
55°	10.0
57.5°	6.4
60°	4.6
62.5°	2.7
65°	1.4
67.5°	0.9
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)