

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748005

Luminaire Tested: LD4D40BD010-EU4DR6040509024-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748005  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR6040509024-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2905.8 lumens  
Efficiency: N/A  
Efficacy: 82.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P748005  
CATALOG NUMBER: LD4D40BD010-EU4DR6040509024-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P748005

CATALOG NUMBER: LD4D40BD010-EU4DR6040509024-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	377070
5°	386341
10°	391008
15°	372488
20°	328413
25°	265633
30°	179682
35°	90033
40°	14605
45°	14293
50°	14584
55°	14801
60°	15209
65°	15564
70°	15941
75°	16126
80°	15541
85°	12912

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 16126 cd/sqm



TEST NUMBER: P748005

CATALOG NUMBER: LD4D40BD010-EU4DR6040509024-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	336.7	11.6
10°-20°	910.9	31.3
20°-30°	980.0	33.7
30°-40°	426.0	14.7
40°-50°	71.5	2.5
50°-60°	69.6	2.4
60°-70°	59.5	2.0
70°-80°	39.8	1.4
80°-90°	11.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2227.5	76.7
0°-40°	2653.5	91.3
0°-60°	2794.6	96.2
0°-90°	2905.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2905.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3451	
5°	3522	337
15°	3293	911
25°	2203	980
35°	675	426
45°	92	72
55°	78	70
65°	60	59
75°	38	40
85°	10	12
90°	0	



TEST NUMBER: P748005

CATALOG NUMBER: LD4D40BD010-EU4DR6040509024-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3451.1
2.5°	3548.1
5°	3522.5
7.5°	3530.6
10°	3524.3
12.5°	3451.5
15°	3293.0
17.5°	3080.1
20°	2824.5
22.5°	2551.0
25°	2203.4
27.5°	1762.4
30°	1424.2
32.5°	1097.7
35°	675.0
37.5°	288.8
40°	102.4
42.5°	94.3
45°	92.5
47.5°	89.4
50°	85.8
52.5°	81.7
55°	77.7
57.5°	73.7
60°	69.6
62.5°	65.1
65°	60.2
67.5°	55.2
70°	49.9
72.5°	44.0
75°	38.2
77.5°	31.4
80°	24.7
82.5°	17.5
85°	10.3
87.5°	3.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)