

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745938

Luminaire Tested: LD4D30D010-EU4DR2520359035-4LBSQW1MW

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745938  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR2520359035-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2147.0 lumens  
Efficiency: N/A  
Efficacy: 74.0 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745938

CATALOG NUMBER: LD4D30D010-EU4DR2520359035-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P745938

CATALOG NUMBER: LD4D30D010-EU4DR2520359035-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																																				
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																																				
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82																																				
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																																				
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	889721
5°	828662
10°	591111
15°	348146
20°	216616
25°	118880
30°	54364
35°	20594
40°	9328
45°	5609
50°	2329
55°	1486
60°	1049
65°	724
70°	96
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5609 cd/sqm



TEST NUMBER: P745938

CATALOG NUMBER: LD4D30D010-EU4DR2520359035-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	649.3	30.2
10°-20°	879.5	41.0
20°-30°	465.4	21.7
30°-40°	114.9	5.4
40°-50°	28.0	1.3
50°-60°	7.4	0.3
60°-70°	2.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1994.2	92.9
0°-40°	2109.1	98.2
0°-60°	2144.5	99.9
0°-90°	2147.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2147.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8143	
5°	7555	649
15°	3078	879
25°	986	465
35°	154	115
45°	36	28
55°	8	7
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745938

CATALOG NUMBER: LD4D30D010-EU4DR2520359035-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8143.1
2.5°	8009.3
5°	7555.4
7.5°	6643.6
10°	5327.9
12.5°	4027.6
15°	3077.8
17.5°	2398.7
20°	1863.0
22.5°	1397.2
25°	986.1
27.5°	661.3
30°	430.9
32.5°	262.2
35°	154.4
37.5°	94.5
40°	65.4
42.5°	50.0
45°	36.3
47.5°	21.9
50°	13.7
52.5°	9.9
55°	7.8
57.5°	6.2
60°	4.8
62.5°	3.8
65°	2.8
67.5°	1.0
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)