

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747705

Luminaire Tested: LD4D40BD010-EU4DR4040509027-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P747705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR4040509027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3256.8 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747705
CATALOG NUMBER: LD4D40BD010-EU4DR4040509027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P747705

CATALOG NUMBER: LD4D40BD010-EU4DR4040509027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96					96			
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92					92			
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88					88			
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84					84			
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81					81			
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77					77			
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74					74			
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72					72			
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	72	70	69					69			
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67					67			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	828502
5°	824472
10°	779309
15°	662515
20°	451546
25°	188405
30°	59234
35°	27530
40°	15233
45°	6984
50°	3383
55°	1848
60°	961
65°	336
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6984 cd/sqm



TEST NUMBER: P747705

CATALOG NUMBER: LD4D40BD010-EU4DR4040509027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	701.9	21.6
10°-20°	1572.5	48.3
20°-30°	787.1	24.2
30°-40°	144.3	4.4
40°-50°	39.8	1.2
50°-60°	9.3	0.3
60°-70°	1.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3061.5	94.0
0°-40°	3205.8	98.4
0°-60°	3255.0	99.9
0°-90°	3256.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3256.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7583	
5°	7517	702
15°	5857	1572
25°	1563	787
35°	206	144
45°	45	40
55°	10	9
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P747705

CATALOG NUMBER: LD4D40BD010-EU4DR4040509027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7582.8
2.5°	7571.7
5°	7517.2
7.5°	7343.6
10°	7024.2
12.5°	6526.3
15°	5857.0
17.5°	4986.5
20°	3883.5
22.5°	2647.6
25°	1562.8
27.5°	826.1
30°	469.5
32.5°	303.4
35°	206.4
37.5°	147.5
40°	106.8
42.5°	73.1
45°	45.2
47.5°	28.8
50°	19.9
52.5°	14.2
55°	9.7
57.5°	6.2
60°	4.4
62.5°	2.7
65°	1.3
67.5°	0.9
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)