

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748085

Luminaire Tested: LD4D40BD010-EU4DR6540509027-4LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748085  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR6540509027-4LBCSSQMMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3213.3 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P748085

CATALOG NUMBER: LD4D40BD010-EU4DR6540509027-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P748085  
 CATALOG NUMBER: LD4D40BD010-EU4DR6540509027-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	170399
5°	169965
10°	169819
15°	164589
20°	149836
25°	130571
30°	108597
35°	86050
40°	62106
45°	39233
50°	20453
55°	10875
60°	5712
65°	3137
70°	1315
75°	1444
80°	1009
85°	871

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 39233 cd/sqm



TEST NUMBER: P748085

CATALOG NUMBER: LD4D40BD010-EU4DR6540509027-4LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	275.9	8.6
10°-20°	755.5	23.5
20°-30°	923.5	28.7
30°-40°	749.3	23.3
40°-50°	373.4	11.6
50°-60°	104.2	3.2
60°-70°	23.7	0.7
70°-80°	6.2	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1955.0	60.8
0°-40°	2704.3	84.2
0°-60°	3181.9	99.0
0°-90°	3213.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3213.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2918	
5°	2899	276
15°	2722	756
25°	2026	924
35°	1207	749
45°	475	373
55°	107	104
65°	23	24
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P748085

CATALOG NUMBER: LD4D40BD010-EU4DR6540509027-4LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2917.6
2.5°	2915.4
5°	2899.1
7.5°	2889.7
10°	2863.5
12.5°	2810.4
15°	2722.1
17.5°	2584.0
20°	2410.8
22.5°	2223.9
25°	2026.2
27.5°	1814.8
30°	1610.3
32.5°	1408.4
35°	1206.9
37.5°	1005.8
40°	814.6
42.5°	635.4
45°	475.0
47.5°	331.0
50°	225.1
52.5°	155.2
55°	106.8
57.5°	72.0
60°	48.9
62.5°	33.9
65°	22.7
67.5°	11.6
70°	7.7
72.5°	7.3
75°	6.4
77.5°	4.3
80°	3.0
82.5°	2.1
85°	1.3
87.5°	0.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)