

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746551

Luminaire Tested: LD4D30D010-EU4DR6520359035-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P746551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR6520359035-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2487.9 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746551
CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P746551

CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131934
5°	131600
10°	131485
15°	127434
20°	116013
25°	101096
30°	84083
35°	66621
40°	48085
45°	30379
50°	15837
55°	8421
60°	4415
65°	2432
70°	1025
75°	1128
80°	774
85°	670

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30379 cd/sqm



TEST NUMBER: P746551

CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.6	8.6
10°-20°	585.0	23.5
20°-30°	715.1	28.7
30°-40°	580.2	23.3
40°-50°	289.1	11.6
50°-60°	80.6	3.2
60°-70°	18.3	0.7
70°-80°	4.8	0.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1513.7	60.8
0°-40°	2093.8	84.2
0°-60°	2463.6	99.0
0°-90°	2487.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2487.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2259	
5°	2245	214
15°	2108	585
25°	1569	715
35°	934	580
45°	368	289
55°	83	81
65°	18	18
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P746551

CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2259.0
2.5°	2257.3
5°	2244.7
7.5°	2237.4
10°	2217.1
12.5°	2176.0
15°	2107.6
17.5°	2000.7
20°	1866.6
22.5°	1721.8
25°	1568.8
27.5°	1405.2
30°	1246.8
32.5°	1090.5
35°	934.4
37.5°	778.8
40°	630.7
42.5°	491.9
45°	367.8
47.5°	256.3
50°	174.3
52.5°	120.1
55°	82.7
57.5°	55.7
60°	37.8
62.5°	26.2
65°	17.6
67.5°	8.9
70°	6.0
72.5°	5.6
75°	5.0
77.5°	3.3
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)