

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746575

Luminaire Tested: LD4D30D010-EU4DR6520359040-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P746575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR6520359040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2290.4 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746575

CATALOG NUMBER: LD4D30D010-EU4DR6520359040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P746575

CATALOG NUMBER: LD4D30D010-EU4DR6520359040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246383
5°	246589
10°	255276
15°	255697
20°	235406
25°	200581
30°	153554
35°	108480
40°	64041
45°	25990
50°	9434
55°	5258
60°	3016
65°	1655
70°	1725
75°	1351
80°	1384
85°	1254

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25990 cd/sqm



TEST NUMBER: P746575

CATALOG NUMBER: LD4D30D010-EU4DR6520359040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.1	9.5
10°-20°	626.4	27.3
20°-30°	751.5	32.8
30°-40°	505.0	22.0
40°-50°	151.2	6.6
50°-60°	26.7	1.2
60°-70°	7.6	0.3
70°-80°	3.7	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1595.0	69.6
0°-40°	2100.0	91.7
0°-60°	2277.9	99.5
0°-90°	2290.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2290.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2255	
5°	2248	217
15°	2260	626
25°	1664	752
35°	813	505
45°	168	151
55°	28	27
65°	6	8
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P746575

CATALOG NUMBER: LD4D30D010-EU4DR6520359040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2255.0
2.5°	2264.6
5°	2248.3
7.5°	2282.3
10°	2300.9
12.5°	2296.4
15°	2260.5
17.5°	2172.7
20°	2024.6
22.5°	1850.3
25°	1663.8
27.5°	1453.3
30°	1217.1
32.5°	1003.0
35°	813.3
37.5°	625.8
40°	449.0
42.5°	293.2
45°	168.2
47.5°	89.1
50°	55.5
52.5°	38.4
55°	27.6
57.5°	19.9
60°	13.8
62.5°	9.0
65°	6.4
67.5°	5.8
70°	5.4
72.5°	4.2
75°	3.2
77.5°	2.9
80°	2.2
82.5°	1.6
85°	1.0
87.5°	0.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)