

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748098

Luminaire Tested: LD4D40BD010-EU4DR6540509030-4LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748098  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR6540509030-4LBCSSQMMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3310.4 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P748098  
CATALOG NUMBER: LD4D40BD010-EU4DR6540509030-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P748098

CATALOG NUMBER: LD4D40BD010-EU4DR6540509030-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	175545
5°	175101
10°	174955
15°	169560
20°	154361
25°	134515
30°	111881
35°	88652
40°	63981
45°	40422
50°	21071
55°	11201
60°	5887
65°	3234
70°	1366
75°	1489
80°	1043
85°	871

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 40422 cd/sqm



TEST NUMBER: P748098

CATALOG NUMBER: LD4D40BD010-EU4DR6540509030-4LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	284.2	8.6
10°-20°	778.4	23.5
20°-30°	951.4	28.7
30°-40°	772.0	23.3
40°-50°	384.7	11.6
50°-60°	107.3	3.2
60°-70°	24.4	0.7
70°-80°	6.3	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2014.1	60.8
0°-40°	2786.0	84.2
0°-60°	3278.0	99.0
0°-90°	3310.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3310.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3006	
5°	2987	284
15°	2804	778
25°	2087	951
35°	1243	772
45°	489	385
55°	110	107
65°	23	24
75°	7	6
85°	1	2
90°	0	



TEST NUMBER: P748098

CATALOG NUMBER: LD4D40BD010-EU4DR6540509030-4LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3005.7
2.5°	3003.5
5°	2986.7
7.5°	2977.0
10°	2950.1
12.5°	2895.3
15°	2804.3
17.5°	2662.1
20°	2483.6
22.5°	2291.1
25°	2087.4
27.5°	1869.7
30°	1659.0
32.5°	1451.0
35°	1243.4
37.5°	1036.2
40°	839.2
42.5°	654.6
45°	489.4
47.5°	341.0
50°	231.9
52.5°	159.9
55°	110.0
57.5°	74.2
60°	50.4
62.5°	34.9
65°	23.4
67.5°	11.9
70°	8.0
72.5°	7.5
75°	6.6
77.5°	4.4
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)