

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748186

Luminaire Tested: LD4D40BD010-EU4DR7040509030-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748186  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR7040509030-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2345.6 lumens  
Efficiency: N/A  
Efficacy: 66.6 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P748186  
CATALOG NUMBER: LD4D40BD010-EU4DR7040509030-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P748186  
 CATALOG NUMBER: LD4D40BD010-EU4DR7040509030-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	288132
5°	279570
10°	271785
15°	268218
20°	250463
25°	188152
30°	133014
35°	47111
40°	24775
45°	26392
50°	27333
55°	27831
60°	28014
65°	27430
70°	25876
75°	23978
80°	21267
85°	17300

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 28022 cd/sqm



TEST NUMBER: P748186

CATALOG NUMBER: LD4D40BD010-EU4DR7040509030-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	240.4	10.3
10°-20°	659.5	28.1
20°-30°	726.3	31.0
30°-40°	277.5	11.8
40°-50°	131.0	5.6
50°-60°	130.3	5.6
60°-70°	104.3	4.4
70°-80°	60.0	2.6
80°-90°	16.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1626.3	69.3
0°-40°	1903.8	81.2
0°-60°	2165.1	92.3
0°-90°	2345.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2345.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2637	
5°	2549	240
15°	2371	659
25°	1561	726
35°	353	278
45°	171	131
55°	146	130
65°	106	104
75°	57	60
85°	14	16
90°	0	



TEST NUMBER: P748186

CATALOG NUMBER: LD4D40BD010-EU4DR7040509030-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2637.1
2.5°	2609.6
5°	2549.0
7.5°	2498.5
10°	2449.7
12.5°	2408.3
15°	2371.2
17.5°	2281.4
20°	2154.1
22.5°	1879.3
25°	1560.7
27.5°	1358.7
30°	1054.3
32.5°	681.0
35°	353.2
37.5°	190.8
40°	173.7
42.5°	172.4
45°	170.8
47.5°	167.0
50°	160.8
52.5°	153.7
55°	146.1
57.5°	137.8
60°	128.2
62.5°	117.3
65°	106.1
67.5°	93.5
70°	81.0
72.5°	68.5
75°	56.8
77.5°	44.7
80°	33.8
82.5°	23.8
85°	13.8
87.5°	5.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)