

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746187

Luminaire Tested: LD4D30D010-EU4DR4020359050-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P746187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR4020359050-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2826.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746187

CATALOG NUMBER: LD4D30D010-EU4DR4020359050-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P746187

CATALOG NUMBER: LD4D30D010-EU4DR4020359050-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																										
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96									96																										
	2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92									92																										
	3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88									88																										
	4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84									84																										
	5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81									81																										
	6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77									77																										
	7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74									74																										
	8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72									72																										
	9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	72	70	69									69																										
	10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67									67																										

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	718903
5°	715408
10°	676218
15°	574862
20°	391816
25°	163486
30°	51399
35°	23889
40°	13208
45°	6057
50°	2941
55°	1619
60°	830
65°	284
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6057 cd/sqm



TEST NUMBER: P746187

CATALOG NUMBER: LD4D30D010-EU4DR4020359050-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	609.1	21.6
10°-20°	1364.5	48.3
20°-30°	683.0	24.2
30°-40°	125.2	4.4
40°-50°	34.5	1.2
50°-60°	8.1	0.3
60°-70°	1.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2656.5	94.0
0°-40°	2781.7	98.4
0°-60°	2824.4	99.9
0°-90°	2826.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2826.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6580	
5°	6523	609
15°	5082	1364
25°	1356	683
35°	179	125
45°	39	35
55°	8	8
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746187

CATALOG NUMBER: LD4D30D010-EU4DR4020359050-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6579.7
2.5°	6570.0
5°	6522.8
7.5°	6372.1
10°	6095.0
12.5°	5662.9
15°	5082.1
17.5°	4326.9
20°	3369.8
22.5°	2297.4
25°	1356.1
27.5°	716.9
30°	407.4
32.5°	263.3
35°	179.1
37.5°	128.0
40°	92.6
42.5°	63.4
45°	39.2
47.5°	25.0
50°	17.3
52.5°	12.3
55°	8.5
57.5°	5.4
60°	3.8
62.5°	2.3
65°	1.1
67.5°	0.7
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)