

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747225

Luminaire Tested: LD4D35BD010-EU4DR6020359024-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P747225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6020359024-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2468.4 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747225
CATALOG NUMBER: LD4D35BD010-EU4DR6020359024-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P747225

CATALOG NUMBER: LD4D35BD010-EU4DR6020359024-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	320309
5°	328179
10°	332151
15°	316417
20°	278985
25°	225644
30°	152633
35°	76482
40°	12409
45°	12145
50°	12392
55°	12572
60°	12915
65°	13211
70°	13513
75°	13678
80°	13213
85°	11032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 13678 cd/sqm



TEST NUMBER: P747225

CATALOG NUMBER: LD4D35BD010-EU4DR6020359024-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.0	11.6
10°-20°	773.7	31.3
20°-30°	832.5	33.7
30°-40°	361.9	14.7
40°-50°	60.8	2.5
50°-60°	59.1	2.4
60°-70°	50.5	2.0
70°-80°	33.8	1.4
80°-90°	10.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1892.2	76.7
0°-40°	2254.1	91.3
0°-60°	2373.9	96.2
0°-90°	2468.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2468.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2932	
5°	2992	286
15°	2797	774
25°	1872	832
35°	573	362
45°	79	61
55°	66	59
65°	51	51
75°	32	34
85°	9	10
90°	0	



TEST NUMBER: P747225

CATALOG NUMBER: LD4D35BD010-EU4DR6020359024-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2931.6
2.5°	3014.0
5°	2992.2
7.5°	2999.1
10°	2993.8
12.5°	2931.9
15°	2797.3
17.5°	2616.4
20°	2399.4
22.5°	2167.0
25°	1871.7
27.5°	1497.1
30°	1209.8
32.5°	932.4
35°	573.4
37.5°	245.3
40°	87.0
42.5°	80.1
45°	78.6
47.5°	75.9
50°	72.9
52.5°	69.4
55°	66.0
57.5°	62.6
60°	59.1
62.5°	55.3
65°	51.1
67.5°	46.9
70°	42.3
72.5°	37.4
75°	32.4
77.5°	26.7
80°	21.0
82.5°	14.9
85°	8.8
87.5°	3.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)