

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748125

Luminaire Tested: LD4D40BD010-EU4DR6540509040-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR6540509040-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3567.0 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748125
CATALOG NUMBER: LD4D40BD010-EU4DR6540509040-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P748125

CATALOG NUMBER: LD4D40BD010-EU4DR6540509040-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	189153
5°	188679
10°	188518
15°	182704
20°	166331
25°	144948
30°	120554
35°	95525
40°	68945
45°	43553
50°	22706
55°	12066
60°	6343
65°	3483
70°	1469
75°	1602
80°	1110
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43553 cd/sqm



TEST NUMBER: P748125

CATALOG NUMBER: LD4D40BD010-EU4DR6540509040-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.3	8.6
10°-20°	838.7	23.5
20°-30°	1025.2	28.7
30°-40°	831.8	23.3
40°-50°	414.5	11.6
50°-60°	115.6	3.2
60°-70°	26.3	0.7
70°-80°	6.8	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2170.2	60.8
0°-40°	3002.0	84.2
0°-60°	3532.1	99.0
0°-90°	3567.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3567.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3239	
5°	3218	306
15°	3022	839
25°	2249	1025
35°	1340	832
45°	527	414
55°	118	116
65°	25	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P748125

CATALOG NUMBER: LD4D40BD010-EU4DR6540509040-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3238.7
2.5°	3236.3
5°	3218.3
7.5°	3207.8
10°	3178.8
12.5°	3119.7
15°	3021.7
17.5°	2868.5
20°	2676.2
22.5°	2468.7
25°	2249.3
27.5°	2014.6
30°	1787.6
32.5°	1563.4
35°	1339.8
37.5°	1116.5
40°	904.3
42.5°	705.3
45°	527.3
47.5°	367.4
50°	249.9
52.5°	172.3
55°	118.5
57.5°	80.0
60°	54.3
62.5°	37.6
65°	25.2
67.5°	12.9
70°	8.6
72.5°	8.1
75°	7.1
77.5°	4.8
80°	3.3
82.5°	2.4
85°	1.4
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)