

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747159

Luminaire Tested: LD4D35BD010-EU4DR5520359027-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P747159
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR5520359027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2579.8 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747159
CATALOG NUMBER: LD4D35BD010-EU4DR5520359027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P747159
 CATALOG NUMBER: LD4D35BD010-EU4DR5520359027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94					94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87					87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81					81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75					75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70					70			
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65					65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61					61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57					57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54					54			
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50					50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	316070
5°	303523
10°	302373
15°	293692
20°	263335
25°	217628
30°	164391
35°	119204
40°	76278
45°	34844
50°	11389
55°	4915
60°	2120
65°	284
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34844 cd/sqm



TEST NUMBER: P747159

CATALOG NUMBER: LD4D35BD010-EU4DR5520359027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.3	10.2
10°-20°	718.7	27.9
20°-30°	819.0	31.7
30°-40°	557.6	21.6
40°-50°	192.1	7.4
50°-60°	26.6	1.0
60°-70°	2.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1801.0	69.8
0°-40°	2358.5	91.4
0°-60°	2577.2	99.9
0°-90°	2579.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2579.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2893	
5°	2767	263
15°	2596	719
25°	1805	819
35°	894	558
45°	226	192
55°	26	27
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P747159

CATALOG NUMBER: LD4D35BD010-EU4DR5520359027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2892.8
2.5°	2826.5
5°	2767.4
7.5°	2738.3
10°	2725.4
12.5°	2682.4
15°	2596.4
17.5°	2459.8
20°	2264.8
22.5°	2039.7
25°	1805.2
27.5°	1561.1
30°	1303.0
32.5°	1084.4
35°	893.7
37.5°	712.3
40°	534.8
42.5°	370.7
45°	225.5
47.5°	121.5
50°	67.0
52.5°	39.8
55°	25.8
57.5°	16.5
60°	9.7
62.5°	4.3
65°	1.1
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)