

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747238

Luminaire Tested: LD4D35BD010-EU4DR6020359027-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P747238  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR6020359027-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2796.2 lumens  
Efficiency: N/A  
Efficacy: 90.8 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P747238  
CATALOG NUMBER: LD4D35BD010-EU4DR6020359027-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P747238

CATALOG NUMBER: LD4D35BD010-EU4DR6020359027-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	362833
5°	371754
10°	376252
15°	358428
20°	316018
25°	255603
30°	172894
35°	86645
40°	14049
45°	13752
50°	14023
55°	14249
60°	14641
65°	14969
70°	15334
75°	15493
80°	14975
85°	12411

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 15493 cd/sqm



TEST NUMBER: P747238

CATALOG NUMBER: LD4D35BD010-EU4DR6020359027-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	324.0	11.6
10°-20°	876.5	31.3
20°-30°	943.0	33.7
30°-40°	409.9	14.7
40°-50°	68.8	2.5
50°-60°	67.0	2.4
60°-70°	57.3	2.0
70°-80°	38.3	1.4
80°-90°	11.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2143.4	76.7
0°-40°	2553.3	91.3
0°-60°	2689.1	96.2
0°-90°	2796.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2796.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3321	
5°	3390	324
15°	3169	876
25°	2120	943
35°	650	410
45°	89	69
55°	75	67
65°	58	57
75°	37	38
85°	10	11
90°	0	



TEST NUMBER: P747238

CATALOG NUMBER: LD4D35BD010-EU4DR6020359027-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3320.8
2.5°	3414.2
5°	3389.5
7.5°	3397.3
10°	3391.3
12.5°	3321.3
15°	3168.7
17.5°	2963.8
20°	2717.9
22.5°	2454.7
25°	2120.2
27.5°	1695.8
30°	1370.4
32.5°	1056.2
35°	649.6
37.5°	277.9
40°	98.5
42.5°	90.8
45°	89.0
47.5°	86.0
50°	82.5
52.5°	78.7
55°	74.8
57.5°	70.9
60°	67.0
62.5°	62.7
65°	57.9
67.5°	53.2
70°	48.0
72.5°	42.4
75°	36.7
77.5°	30.3
80°	23.8
82.5°	16.9
85°	9.9
87.5°	3.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)