

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747305

Luminaire Tested: LD4D35BD010-EU4DR6520359027-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P747305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR6520359027-4LBCSSQMMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2729.5 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747305
CATALOG NUMBER: LD4D35BD010-EU4DR6520359027-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P747305
 CATALOG NUMBER: LD4D35BD010-EU4DR6520359027-4LBCSSQMMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144748
5°	144381
10°	144259
15°	139811
20°	127281
25°	110917
30°	92250
35°	73095
40°	52759
45°	33327
50°	17372
55°	9235
60°	4848
65°	2667
70°	1127
75°	1241
80°	841
85°	737

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33327 cd/sqm



TEST NUMBER: P747305

CATALOG NUMBER: LD4D35BD010-EU4DR6520359027-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.4	8.6
10°-20°	641.8	23.5
20°-30°	784.5	28.7
30°-40°	636.5	23.3
40°-50°	317.2	11.6
50°-60°	88.5	3.2
60°-70°	20.1	0.7
70°-80°	5.2	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1660.7	60.8
0°-40°	2297.2	84.2
0°-60°	2702.9	99.0
0°-90°	2729.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2729.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2478	
5°	2463	234
15°	2312	642
25°	1721	785
35°	1025	637
45°	404	317
55°	91	88
65°	19	20
75°	6	5
85°	1	1
90°	0	



TEST NUMBER: P747305

CATALOG NUMBER: LD4D35BD010-EU4DR6520359027-4LBCSSQMMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2478.4
2.5°	2476.5
5°	2462.7
7.5°	2454.7
10°	2432.5
12.5°	2387.3
15°	2312.3
17.5°	2195.0
20°	2047.9
22.5°	1889.1
25°	1721.2
27.5°	1541.7
30°	1367.9
32.5°	1196.4
35°	1025.2
37.5°	854.4
40°	692.0
42.5°	539.7
45°	403.5
47.5°	281.2
50°	191.2
52.5°	131.8
55°	90.7
57.5°	61.2
60°	41.5
62.5°	28.8
65°	19.3
67.5°	9.8
70°	6.6
72.5°	6.2
75°	5.5
77.5°	3.6
80°	2.5
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)