

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746952

Luminaire Tested: LD4D35BD010-EU4DR4020359035-4LBSQW1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P746952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR4020359035-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3056.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P746952
CATALOG NUMBER: LD4D35BD010-EU4DR4020359035-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P746952

CATALOG NUMBER: LD4D35BD010-EU4DR4020359035-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	97	96	95	93	92	91	89	88	87	84	82	81	77	74	72	69	68														
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96	95	93	92	91	89	88	87	84	82	81	77	74	72	69	68																				
	2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92	91	89	88	87	84	82	81	77	74	72	69	68																							
	3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88	87	84	82	81	77	74	72	69	68																										
	4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84	82	81	77	74	72	69	68																												
	5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81	77	74	72	69	68																														
	6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77	74	72	69	68																															
	7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74	72	69	68																																
	8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72	69	68																																	
	9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	72	70	69	68																																		
	10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	69	68																																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	777434
5°	773647
10°	731269
15°	621669
20°	423710
25°	176795
30°	55588
35°	25836
40°	14292
45°	6552
50°	3179
55°	1733
60°	918
65°	310
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6552 cd/sqm



TEST NUMBER: P746952

CATALOG NUMBER: LD4D35BD010-EU4DR4020359035-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	658.6	21.6
10°-20°	1475.5	48.3
20°-30°	738.6	24.2
30°-40°	135.4	4.4
40°-50°	37.4	1.2
50°-60°	8.8	0.3
60°-70°	1.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2872.8	94.0
0°-40°	3008.2	98.4
0°-60°	3054.3	99.9
0°-90°	3056.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3056.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7115	
5°	7054	659
15°	5496	1476
25°	1466	739
35°	194	135
45°	42	37
55°	9	9
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746952

CATALOG NUMBER: LD4D35BD010-EU4DR4020359035-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7115.4
2.5°	7105.0
5°	7053.8
7.5°	6890.9
10°	6591.2
12.5°	6124.0
15°	5495.9
17.5°	4679.1
20°	3644.1
22.5°	2484.4
25°	1466.5
27.5°	775.2
30°	440.6
32.5°	284.7
35°	193.7
37.5°	138.4
40°	100.2
42.5°	68.6
45°	42.4
47.5°	27.0
50°	18.7
52.5°	13.3
55°	9.1
57.5°	5.8
60°	4.2
62.5°	2.5
65°	1.2
67.5°	0.8
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)