

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746720

Luminaire Tested: LD4D35BD010-EU4DR2520359040-4LBCSSQMMS

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746720  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR2520359040-4LBCSSQMMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2778.0 lumens  
Efficiency: N/A  
Efficacy: 90.2 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P746720  
CATALOG NUMBER: LD4D35BD010-EU4DR2520359040-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P746720

CATALOG NUMBER: LD4D35BD010-EU4DR2520359040-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																			
	2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																			
	3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																																			
	4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																																			
	5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82																																			
	6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																																			
	7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77																																			
	8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																			
	9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																																			
	10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1151248
5°	1072235
10°	764853
15°	450469
20°	280287
25°	153829
30°	70349
35°	26637
40°	12066
45°	7247
50°	3009
55°	1943
60°	1355
65°	905
70°	128
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7247 cd/sqm



TEST NUMBER: P746720

CATALOG NUMBER: LD4D35BD010-EU4DR2520359040-4LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	840.2	30.2
10°-20°	1138.0	41.0
20°-30°	602.2	21.7
30°-40°	148.6	5.4
40°-50°	36.3	1.3
50°-60°	9.5	0.3
60°-70°	3.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2580.4	92.9
0°-40°	2729.0	98.2
0°-60°	2774.8	99.9
0°-90°	2778.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2778.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10537	
5°	9776	840
15°	3982	1138
25°	1276	602
35°	200	149
45°	47	36
55°	10	10
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P746720

CATALOG NUMBER: LD4D35BD010-EU4DR2520359040-4LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10536.7
2.5°	10363.5
5°	9776.2
7.5°	8596.4
10°	6893.9
12.5°	5211.4
15°	3982.4
17.5°	3103.7
20°	2410.6
22.5°	1807.9
25°	1276.0
27.5°	855.7
30°	557.6
32.5°	339.2
35°	199.7
37.5°	122.2
40°	84.6
42.5°	64.7
45°	46.9
47.5°	28.3
50°	17.7
52.5°	12.8
55°	10.2
57.5°	8.0
60°	6.2
62.5°	4.9
65°	3.5
67.5°	1.3
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)