

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748878

Luminaire Tested: LD4D45BD010-EU4DR6540509030-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748878
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6540509030-4LBCSSQMMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3626.2 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748878

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P748878
 CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBCSSQMMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192289
5°	191804
10°	191644
15°	185734
20°	169091
25°	147352
30°	122557
35°	97108
40°	70088
45°	44279
50°	23079
55°	12270
60°	6448
65°	3538
70°	1486
75°	1647
80°	1144
85°	1005

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 44279 cd/sqm



TEST NUMBER: P748878

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.4	8.6
10°-20°	852.6	23.5
20°-30°	1042.2	28.7
30°-40°	845.6	23.3
40°-50°	421.4	11.6
50°-60°	117.5	3.2
60°-70°	26.7	0.7
70°-80°	6.9	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2206.2	60.8
0°-40°	3051.8	84.2
0°-60°	3590.7	99.0
0°-90°	3626.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3626.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3292	
5°	3272	311
15°	3072	853
25°	2287	1042
35°	1362	846
45°	536	421
55°	120	118
65°	26	27
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P748878

CATALOG NUMBER: LD4D45BD010-EU4DR6540509030-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3292.4
2.5°	3290.0
5°	3271.6
7.5°	3261.0
10°	3231.5
12.5°	3171.5
15°	3071.8
17.5°	2916.0
20°	2720.6
22.5°	2509.6
25°	2286.6
27.5°	2048.0
30°	1817.3
32.5°	1589.4
35°	1362.0
37.5°	1135.1
40°	919.3
42.5°	717.0
45°	536.1
47.5°	373.5
50°	254.0
52.5°	175.1
55°	120.5
57.5°	81.3
60°	55.2
62.5°	38.2
65°	25.6
67.5°	13.1
70°	8.7
72.5°	8.2
75°	7.3
77.5°	4.8
80°	3.4
82.5°	2.4
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)