

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747446

Luminaire Tested: LD4D35BD010-EU4DR7020359050-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P747446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR7020359050-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2827.0 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747446
CATALOG NUMBER: LD4D35BD010-EU4DR7020359050-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P747446

CATALOG NUMBER: LD4D35BD010-EU4DR7020359050-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	347285
5°	336964
10°	327569
15°	323272
20°	301868
25°	226778
30°	160316
35°	56781
40°	29852
45°	31800
50°	32925
55°	33545
60°	33762
65°	33041
70°	31179
75°	28875
80°	25672
85°	20810

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 33777 cd/sqm



TEST NUMBER: P747446

CATALOG NUMBER: LD4D35BD010-EU4DR7020359050-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.8	10.3
10°-20°	794.9	28.1
20°-30°	875.4	31.0
30°-40°	334.5	11.8
40°-50°	157.9	5.6
50°-60°	157.0	5.6
60°-70°	125.7	4.4
70°-80°	72.2	2.6
80°-90°	19.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1960.1	69.3
0°-40°	2294.5	81.2
0°-60°	2609.5	92.3
0°-90°	2827.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2827.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3178	
5°	3072	290
15°	2858	795
25°	1881	875
35°	426	334
45°	206	158
55°	176	157
65°	128	126
75°	68	72
85°	17	20
90°	0	



TEST NUMBER: P747446

CATALOG NUMBER: LD4D35BD010-EU4DR7020359050-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3178.5
2.5°	3145.2
5°	3072.3
7.5°	3011.4
10°	2952.5
12.5°	2902.7
15°	2857.9
17.5°	2749.7
20°	2596.2
22.5°	2265.1
25°	1881.1
27.5°	1637.5
30°	1270.7
32.5°	820.8
35°	425.7
37.5°	230.0
40°	209.3
42.5°	207.8
45°	205.8
47.5°	201.3
50°	193.7
52.5°	185.2
55°	176.1
57.5°	166.1
60°	154.5
62.5°	141.4
65°	127.8
67.5°	112.7
70°	97.6
72.5°	82.5
75°	68.4
77.5°	53.8
80°	40.8
82.5°	28.7
85°	16.6
87.5°	6.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)