

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748824

Luminaire Tested: LD4D45BD010-EU4DR6040509035-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6040509035-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3753.7 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748824

CATALOG NUMBER: LD4D45BD010-EU4DR6040509035-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P748824

CATALOG NUMBER: LD4D45BD010-EU4DR6040509035-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	487095
5°	499068
10°	505094
15°	481180
20°	424245
25°	343138
30°	232103
35°	116310
40°	18870
45°	18465
50°	18834
55°	19125
60°	19645
65°	20088
70°	20573
75°	20812
80°	20072
85°	16673

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 20812 cd/sqm



TEST NUMBER: P748824

CATALOG NUMBER: LD4D45BD010-EU4DR6040509035-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	434.9	11.6
10°-20°	1176.6	31.3
20°-30°	1266.0	33.7
30°-40°	550.3	14.7
40°-50°	92.4	2.5
50°-60°	89.9	2.4
60°-70°	76.9	2.0
70°-80°	51.4	1.4
80°-90°	15.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2877.5	76.7
0°-40°	3427.8	91.3
0°-60°	3610.1	96.2
0°-90°	3753.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3753.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4458	
5°	4550	435
15°	4254	1177
25°	2846	1266
35°	872	550
45°	120	92
55°	100	90
65°	78	77
75°	49	51
85°	13	15
90°	0	



TEST NUMBER: P748824

CATALOG NUMBER: LD4D45BD010-EU4DR6040509035-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4458.1
2.5°	4583.4
5°	4550.3
7.5°	4560.8
10°	4552.6
12.5°	4458.7
15°	4253.9
17.5°	3978.9
20°	3648.7
22.5°	3295.4
25°	2846.3
27.5°	2276.6
30°	1839.7
32.5°	1418.0
35°	872.0
37.5°	373.1
40°	132.3
42.5°	121.8
45°	119.5
47.5°	115.5
50°	110.8
52.5°	105.6
55°	100.4
57.5°	95.1
60°	89.9
62.5°	84.1
65°	77.7
67.5°	71.4
70°	64.4
72.5°	56.9
75°	49.3
77.5°	40.6
80°	31.9
82.5°	22.6
85°	13.3
87.5°	4.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)