

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748435

Luminaire Tested: LD4D45BD010-EU4DR3540509040-4LBCSSQMB

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748435  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D45BD010-EU4DR3540509040-4LBCSSQMB  
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4006.3 lumens  
Efficiency: N/A  
Efficacy: 103.5 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P748435  
CATALOG NUMBER: LD4D45BD010-EU4DR3540509040-4LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P748435  
 CATALOG NUMBER: LD4D45BD010-EU4DR3540509040-4LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																											
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																											
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																											
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																											
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																											
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																											
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																											
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																											
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																											
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1204436
5°	1176133
10°	1060003
15°	822731
20°	466638
25°	181545
30°	67725
35°	37120
40°	24261
45°	14772
50°	9400
55°	6648
60°	4851
65°	2637
70°	192
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14772 cd/sqm



TEST NUMBER: P748435

CATALOG NUMBER: LD4D45BD010-EU4DR3540509040-4LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	986.2	24.6
10°-20°	1925.6	48.1
20°-30°	785.3	19.6
30°-40°	187.9	4.7
40°-50°	78.3	2.0
50°-60°	32.4	0.8
60°-70°	10.1	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3697.1	92.3
0°-40°	3885.0	97.0
0°-60°	3995.8	99.7
0°-90°	4006.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4006.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11024	
5°	10724	986
15°	7273	1926
25°	1506	785
35°	278	188
45°	96	78
55°	35	32
65°	10	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P748435

CATALOG NUMBER: LD4D45BD010-EU4DR3540509040-4LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11023.5
2.5°	10957.3
5°	10723.5
7.5°	10257.0
10°	9554.2
12.5°	8564.7
15°	7273.4
17.5°	5694.2
20°	4013.3
22.5°	2559.1
25°	1505.9
27.5°	851.2
30°	536.8
32.5°	376.9
35°	278.3
37.5°	215.2
40°	170.1
42.5°	131.1
45°	95.6
47.5°	71.5
50°	55.3
52.5°	43.9
55°	34.9
57.5°	28.3
60°	22.2
62.5°	16.2
65°	10.2
67.5°	3.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)