

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747461

Luminaire Tested: LD4D40BD010-EU4DR2540509027-4LBCSSQMMS

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P747461  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR2540509027-4LBCSSQMMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3001.1 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P747461  
CATALOG NUMBER: LD4D40BD010-EU4DR2540509027-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P747461

CATALOG NUMBER: LD4D40BD010-EU4DR2540509027-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 |  | 103 | 102 | 101 |  | 99  | 99  | 98  | 96  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98  |  | 99  | 97  | 96  |  | 97  | 95  | 94  | 92  |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 93  |  | 96  | 93  | 91  |  | 94  | 92  | 90  | 89  |
| 4   | 103 | 97  | 93  | 90  | 102 | 96  | 93  | 90  | 94  | 91  | 89  |  | 93  | 90  | 88  |  | 91  | 89  | 87  | 85  |
| 5   | 100 | 93  | 89  | 86  | 98  | 93  | 89  | 86  | 91  | 87  | 85  |  | 89  | 86  | 84  |  | 88  | 85  | 83  | 82  |
| 6   | 97  | 90  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 81  |  | 87  | 83  | 81  |  | 85  | 83  | 80  | 79  |
| 7   | 93  | 87  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 78  |  | 84  | 80  | 78  |  | 83  | 80  | 78  | 77  |
| 8   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 76  |  | 81  | 78  | 75  |  | 80  | 77  | 75  | 74  |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 80  | 76  | 73  |  | 79  | 75  | 73  |  | 78  | 75  | 73  | 72  |
| 10  | 85  | 78  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  |  | 76  | 73  | 71  |  | 76  | 73  | 70  | 69  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1243650 |
| 5°  | 1158300 |
| 10° | 826250  |
| 15° | 486632  |
| 20° | 302786  |
| 25° | 166174  |
| 30° | 75988   |
| 35° | 28784   |
| 40° | 13036   |
| 45° | 7834    |
| 50° | 3247    |
| 55° | 2095    |
| 60° | 1464    |
| 65° | 982     |
| 70° | 160     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7834 cd/sqm



TEST NUMBER: P747461

CATALOG NUMBER: LD4D40BD010-EU4DR2540509027-4LBCSSQMMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 907.6  | 30.2      |
| 10°-20°   | 1229.3 | 41.0      |
| 20°-30°   | 650.5  | 21.7      |
| 30°-40°   | 160.6  | 5.4       |
| 40°-50°   | 39.2   | 1.3       |
| 50°-60°   | 10.3   | 0.3       |
| 60°-70°   | 3.5    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2787.5 | 92.9      |
| 0°-40°    | 2948.1 | 98.2      |
| 0°-60°    | 2997.5 | 99.9      |
| 0°-90°    | 3001.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3001.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 11382 |      |
| 5°  | 10561 | 908  |
| 15° | 4302  | 1229 |
| 25° | 1378  | 651  |
| 35° | 216   | 161  |
| 45° | 51    | 39   |
| 55° | 11    | 10   |
| 65° | 4     | 3    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P747461

CATALOG NUMBER: LD4D40BD010-EU4DR2540509027-4LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 11382.4 |
| 2.5°  | 11195.3 |
| 5°    | 10560.9 |
| 7.5°  | 9286.4  |
| 10°   | 7447.3  |
| 12.5° | 5629.7  |
| 15°   | 4302.1  |
| 17.5° | 3352.8  |
| 20°   | 2604.1  |
| 22.5° | 1953.0  |
| 25°   | 1378.4  |
| 27.5° | 924.3   |
| 30°   | 602.3   |
| 32.5° | 366.5   |
| 35°   | 215.8   |
| 37.5° | 132.0   |
| 40°   | 91.4    |
| 42.5° | 69.9    |
| 45°   | 50.7    |
| 47.5° | 30.6    |
| 50°   | 19.1    |
| 52.5° | 13.9    |
| 55°   | 11.0    |
| 57.5° | 8.6     |
| 60°   | 6.7     |
| 62.5° | 5.3     |
| 65°   | 3.8     |
| 67.5° | 1.4     |
| 70°   | 0.5     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)