

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748992

Luminaire Tested: LD4D45BD010-EU4DR7040509040-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR7040509040-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2717.9 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748992
CATALOG NUMBER: LD4D45BD010-EU4DR7040509040-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P748992

CATALOG NUMBER: LD4D45BD010-EU4DR7040509040-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	333857
5°	323934
10°	314910
15°	310772
20°	290205
25°	218013
30°	154121
35°	54594
40°	28711
45°	30579
50°	31667
55°	32250
60°	32450
65°	31774
70°	29997
75°	27778
80°	24665
85°	20058

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 32475 cd/sqm



TEST NUMBER: P748992

CATALOG NUMBER: LD4D45BD010-EU4DR7040509040-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.6	10.2
10°-20°	764.1	28.1
20°-30°	841.6	31.0
30°-40°	321.6	11.8
40°-50°	151.8	5.6
50°-60°	150.9	5.6
60°-70°	120.9	4.4
70°-80°	69.5	2.6
80°-90°	18.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1884.3	69.3
0°-40°	2205.9	81.2
0°-60°	2508.6	92.3
0°-90°	2717.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2717.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3056	
5°	2954	279
15°	2747	764
25°	1808	842
35°	409	322
45°	198	152
55°	169	151
65°	123	121
75°	66	69
85°	16	19
90°	0	



TEST NUMBER: P748992

CATALOG NUMBER: LD4D45BD010-EU4DR7040509040-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3055.6
2.5°	3023.7
5°	2953.5
7.5°	2895.0
10°	2838.4
12.5°	2790.5
15°	2747.4
17.5°	2643.4
20°	2495.9
22.5°	2177.5
25°	1808.4
27.5°	1574.2
30°	1221.6
32.5°	789.1
35°	409.3
37.5°	221.1
40°	201.3
42.5°	199.8
45°	197.9
47.5°	193.5
50°	186.3
52.5°	178.0
55°	169.3
57.5°	159.7
60°	148.5
62.5°	135.9
65°	122.9
67.5°	108.4
70°	93.9
72.5°	79.3
75°	65.8
77.5°	51.8
80°	39.2
82.5°	27.6
85°	16.0
87.5°	6.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)