

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748018

Luminaire Tested: LD4D40BD010-EU4DR6040509027-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR6040509027-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3291.7 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748018
CATALOG NUMBER: LD4D40BD010-EU4DR6040509027-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P748018

CATALOG NUMBER: LD4D40BD010-EU4DR6040509027-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	427133
5°	437638
10°	442920
15°	421942
20°	372027
25°	300908
30°	203539
35°	101998
40°	16545
45°	16193
50°	16522
55°	16763
60°	17241
65°	17632
70°	18049
75°	18237
80°	17618
85°	14667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 18237 cd/sqm



TEST NUMBER: P748018

CATALOG NUMBER: LD4D40BD010-EU4DR6040509027-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	381.4	11.6
10°-20°	1031.8	31.3
20°-30°	1110.1	33.7
30°-40°	482.6	14.7
40°-50°	81.0	2.5
50°-60°	78.8	2.4
60°-70°	67.4	2.0
70°-80°	45.1	1.4
80°-90°	13.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2523.3	76.7
0°-40°	3005.8	91.3
0°-60°	3165.7	96.2
0°-90°	3291.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3291.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3909	
5°	3990	381
15°	3730	1032
25°	2496	1110
35°	765	483
45°	105	81
55°	88	79
65°	68	67
75°	43	45
85°	12	13
90°	0	



TEST NUMBER: P748018

CATALOG NUMBER: LD4D40BD010-EU4DR6040509027-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3909.3
2.5°	4019.2
5°	3990.2
7.5°	3999.3
10°	3992.2
12.5°	3909.8
15°	3730.2
17.5°	3489.1
20°	3199.6
22.5°	2889.7
25°	2496.0
27.5°	1996.4
30°	1613.3
32.5°	1243.4
35°	764.7
37.5°	327.1
40°	116.0
42.5°	106.8
45°	104.8
47.5°	101.2
50°	97.2
52.5°	92.6
55°	88.0
57.5°	83.4
60°	78.9
62.5°	73.8
65°	68.2
67.5°	62.6
70°	56.5
72.5°	49.9
75°	43.2
77.5°	35.6
80°	28.0
82.5°	19.8
85°	11.7
87.5°	4.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)