

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748849

Luminaire Tested: LD4D45BD010-EU4DR6040509050-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748849
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6040509050-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3513.1 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748849
CATALOG NUMBER: LD4D45BD010-EU4DR6040509050-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P748849

CATALOG NUMBER: LD4D45BD010-EU4DR6040509050-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	455858
5°	467064
10°	472709
15°	450322
20°	397037
25°	321137
30°	217228
35°	108854
40°	17658
45°	17291
50°	17627
55°	17887
60°	18400
65°	18821
70°	19263
75°	19503
80°	18813
85°	15670

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 19503 cd/sqm



TEST NUMBER: P748849

CATALOG NUMBER: LD4D45BD010-EU4DR6040509050-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	407.0	11.6
10°-20°	1101.2	31.3
20°-30°	1184.8	33.7
30°-40°	515.0	14.7
40°-50°	86.5	2.5
50°-60°	84.1	2.4
60°-70°	72.0	2.0
70°-80°	48.1	1.4
80°-90°	14.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2693.0	76.7
0°-40°	3208.0	91.3
0°-60°	3378.6	96.2
0°-90°	3513.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3513.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4172	
5°	4258	407
15°	3981	1101
25°	2664	1185
35°	816	515
45°	112	87
55°	94	84
65°	73	72
75°	46	48
85°	12	14
90°	0	



TEST NUMBER: P748849

CATALOG NUMBER: LD4D45BD010-EU4DR6040509050-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4172.2
2.5°	4289.5
5°	4258.5
7.5°	4268.3
10°	4260.7
12.5°	4172.7
15°	3981.1
17.5°	3723.7
20°	3414.7
22.5°	3084.1
25°	2663.8
27.5°	2130.6
30°	1721.8
32.5°	1327.0
35°	816.1
37.5°	349.1
40°	123.8
42.5°	114.0
45°	111.9
47.5°	108.1
50°	103.7
52.5°	98.8
55°	93.9
57.5°	89.0
60°	84.2
62.5°	78.7
65°	72.8
67.5°	66.8
70°	60.3
72.5°	53.2
75°	46.2
77.5°	38.0
80°	29.9
82.5°	21.2
85°	12.5
87.5°	4.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)