

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748199

Luminaire Tested: LD4D40BD010-EU4DR7040509035-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR7040509035-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2370.4 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748199
CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P748199
 CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	291169
5°	282520
10°	274648
15°	271046
20°	253091
25°	190141
30°	134415
35°	47618
40°	25032
45°	26670
50°	27605
55°	28135
60°	28299
65°	27715
70°	26164
75°	24231
80°	21519
85°	17425

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 28307 cd/sqm



TEST NUMBER: P748199

CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.0	10.2
10°-20°	666.4	28.1
20°-30°	734.0	31.0
30°-40°	280.4	11.8
40°-50°	132.4	5.6
50°-60°	131.6	5.6
60°-70°	105.4	4.4
70°-80°	60.6	2.6
80°-90°	16.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1643.4	69.3
0°-40°	1923.8	81.2
0°-60°	2187.9	92.3
0°-90°	2370.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2370.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2665	
5°	2576	243
15°	2396	666
25°	1577	734
35°	357	280
45°	173	132
55°	148	132
65°	107	105
75°	57	61
85°	14	16
90°	0	



TEST NUMBER: P748199

CATALOG NUMBER: LD4D40BD010-EU4DR7040509035-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	2664.9
2.5°	2637.1
5°	2575.9
7.5°	2524.8
10°	2475.5
12.5°	2433.7
15°	2396.2
17.5°	2305.4
20°	2176.7
22.5°	1899.1
25°	1577.2
27.5°	1373.0
30°	1065.4
32.5°	688.2
35°	357.0
37.5°	192.8
40°	175.5
42.5°	174.3
45°	172.6
47.5°	168.8
50°	162.4
52.5°	155.3
55°	147.7
57.5°	139.2
60°	129.5
62.5°	118.6
65°	107.2
67.5°	94.5
70°	81.9
72.5°	69.2
75°	57.4
77.5°	45.1
80°	34.2
82.5°	24.1
85°	13.9
87.5°	5.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)