

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748069

Luminaire Tested: LD4D40BD010-EU4DR6040509050-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748069  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D40BD010-EU4DR6040509050-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3207.1 lumens  
Efficiency: N/A  
Efficacy: 91.1 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 35.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P748069  
CATALOG NUMBER: LD4D40BD010-EU4DR6040509050-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P748069

CATALOG NUMBER: LD4D40BD010-EU4DR6040509050-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	416163
5°	426396
10°	431548
15°	411105
20°	362469
25°	293168
30°	198304
35°	99370
40°	16117
45°	15776
50°	16097
55°	16344
60°	16782
65°	17167
70°	17570
75°	17773
80°	17177
85°	14291

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 17773 cd/sqm



TEST NUMBER: P748069

CATALOG NUMBER: LD4D40BD010-EU4DR6040509050-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	371.6	11.6
10°-20°	1005.3	31.3
20°-30°	1081.6	33.7
30°-40°	470.1	14.7
40°-50°	79.0	2.5
50°-60°	76.8	2.4
60°-70°	65.7	2.0
70°-80°	43.9	1.4
80°-90°	13.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2458.5	76.7
0°-40°	2928.6	91.3
0°-60°	3084.4	96.2
0°-90°	3207.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3207.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3809	
5°	3888	372
15°	3634	1005
25°	2432	1082
35°	745	470
45°	102	79
55°	86	77
65°	66	66
75°	42	44
85°	11	13
90°	0	



TEST NUMBER: P748069

CATALOG NUMBER: LD4D40BD010-EU4DR6040509050-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3808.9
2.5°	3915.9
5°	3887.7
7.5°	3896.6
10°	3889.7
12.5°	3809.4
15°	3634.4
17.5°	3399.4
20°	3117.4
22.5°	2815.5
25°	2431.8
27.5°	1945.1
30°	1571.8
32.5°	1211.5
35°	745.0
37.5°	318.7
40°	113.0
42.5°	104.1
45°	102.1
47.5°	98.6
50°	94.7
52.5°	90.2
55°	85.8
57.5°	81.3
60°	76.8
62.5°	71.9
65°	66.4
67.5°	61.0
70°	55.0
72.5°	48.6
75°	42.1
77.5°	34.7
80°	27.3
82.5°	19.3
85°	11.4
87.5°	4.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)