

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748785

Luminaire Tested: LD4D45BD010-EU4DR6040509024-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748785  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D45BD010-EU4DR6040509024-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3183.0 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P748785  
CATALOG NUMBER: LD4D45BD010-EU4DR6040509024-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P748785

CATALOG NUMBER: LD4D45BD010-EU4DR6040509024-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	413038
5°	423193
10°	428297
15°	408017
20°	359748
25°	290974
30°	196815
35°	98623
40°	16003
45°	15653
50°	15978
55°	16211
60°	16673
65°	17037
70°	17442
75°	17646
80°	17052
85°	14166

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 17646 cd/sqm



TEST NUMBER: P748785

CATALOG NUMBER: LD4D45BD010-EU4DR6040509024-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	368.8	11.6
10°-20°	997.7	31.3
20°-30°	1073.5	33.7
30°-40°	466.6	14.7
40°-50°	78.4	2.5
50°-60°	76.2	2.4
60°-70°	65.2	2.0
70°-80°	43.6	1.4
80°-90°	13.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2440.0	76.7
0°-40°	2906.6	91.3
0°-60°	3061.2	96.2
0°-90°	3183.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3183.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3780	
5°	3858	369
15°	3607	998
25°	2414	1073
35°	739	467
45°	101	78
55°	85	76
65°	66	65
75°	42	44
85°	11	13
90°	0	



TEST NUMBER: P748785

CATALOG NUMBER: LD4D45BD010-EU4DR6040509024-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3780.3
2.5°	3886.5
5°	3858.5
7.5°	3867.3
10°	3860.4
12.5°	3780.7
15°	3607.1
17.5°	3373.9
20°	3094.0
22.5°	2794.4
25°	2413.6
27.5°	1930.5
30°	1560.0
32.5°	1202.4
35°	739.4
37.5°	316.3
40°	112.2
42.5°	103.3
45°	101.3
47.5°	97.9
50°	94.0
52.5°	89.5
55°	85.1
57.5°	80.7
60°	76.3
62.5°	71.3
65°	65.9
67.5°	60.5
70°	54.6
72.5°	48.2
75°	41.8
77.5°	34.4
80°	27.1
82.5°	19.2
85°	11.3
87.5°	3.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)