

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748941

Luminaire Tested: LD4D45BD010-EU4DR7040509024-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P748941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR7040509024-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2932.3 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748941

CATALOG NUMBER: LD4D45BD010-EU4DR7040509024-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P748941

CATALOG NUMBER: LD4D45BD010-EU4DR7040509024-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	360200
5°	349500
10°	339751
15°	335296
20°	313100
25°	235217
30°	166271
35°	58902
40°	30965
45°	32990
50°	34166
55°	34803
60°	35007
65°	34281
70°	32361
75°	29973
80°	26615
85°	21562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 35017 cd/sqm



TEST NUMBER: P748941

CATALOG NUMBER: LD4D45BD010-EU4DR7040509024-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.6	10.3
10°-20°	824.4	28.1
20°-30°	908.0	31.0
30°-40°	346.9	11.8
40°-50°	163.8	5.6
50°-60°	162.8	5.6
60°-70°	130.4	4.4
70°-80°	74.9	2.6
80°-90°	20.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2033.0	69.3
0°-40°	2379.9	81.2
0°-60°	2706.5	92.3
0°-90°	2932.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2932.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3297	
5°	3187	301
15°	2964	824
25°	1951	908
35°	442	347
45°	214	164
55°	183	163
65°	133	130
75°	71	75
85°	17	20
90°	0	



TEST NUMBER: P748941

CATALOG NUMBER: LD4D45BD010-EU4DR7040509024-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3296.7
2.5°	3262.2
5°	3186.6
7.5°	3123.4
10°	3062.3
12.5°	3010.7
15°	2964.2
17.5°	2852.0
20°	2692.8
22.5°	2349.3
25°	1951.1
27.5°	1698.4
30°	1317.9
32.5°	851.3
35°	441.6
37.5°	238.5
40°	217.1
42.5°	215.6
45°	213.5
47.5°	208.8
50°	201.0
52.5°	192.1
55°	182.7
57.5°	172.2
60°	160.2
62.5°	146.7
65°	132.6
67.5°	116.9
70°	101.3
72.5°	85.6
75°	71.0
77.5°	55.8
80°	42.3
82.5°	29.8
85°	17.2
87.5°	6.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)