

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P749177

Luminaire Tested: LD4D50D010-EU4DR3540509027-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P749177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D50D010-EU4DR3540509027-4LBCSSQMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4317.6 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P749177

CATALOG NUMBER: LD4D50D010-EU4DR3540509027-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P749177

CATALOG NUMBER: LD4D50D010-EU4DR3540509027-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																																				
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																																				
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																																				
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																																				
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																																				
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																																				
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																																				
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																																				
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																																				
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1298007
5°	1267506
10°	1142358
15°	886652
20°	502892
25°	195650
30°	72986
35°	40015
40°	26144
45°	15915
50°	10131
55°	7162
60°	5245
65°	2844
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15915 cd/sqm



TEST NUMBER: P749177

CATALOG NUMBER: LD4D50D010-EU4DR3540509027-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1062.9	24.6
10°-20°	2075.2	48.1
20°-30°	846.3	19.6
30°-40°	202.5	4.7
40°-50°	84.4	2.0
50°-60°	34.9	0.8
60°-70°	10.9	0.3
70°-80°	0.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3984.4	92.3
0°-40°	4186.9	97.0
0°-60°	4306.2	99.7
0°-90°	4317.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4317.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11880	
5°	11557	###
15°	7838	2075
25°	1623	846
35°	300	203
45°	103	84
55°	38	35
65°	11	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P749177

CATALOG NUMBER: LD4D50D010-EU4DR3540509027-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	11879.9
2.5°	11808.6
5°	11556.6
7.5°	11053.9
10°	10296.5
12.5°	9230.1
15°	7838.5
17.5°	6136.6
20°	4325.1
22.5°	2758.0
25°	1622.9
27.5°	917.4
30°	578.5
32.5°	406.2
35°	300.0
37.5°	231.9
40°	183.3
42.5°	141.2
45°	103.0
47.5°	77.1
50°	59.6
52.5°	47.3
55°	37.6
57.5°	30.4
60°	24.0
62.5°	17.5
65°	11.0
67.5°	3.9
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)