

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748251

Luminaire Tested: LD4D45BD010-EU4DR2540509027-4LBSQW1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P748251  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D45BD010-EU4DR2540509027-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2701.2 lumens  
Efficiency: N/A  
Efficacy: 69.8 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P748251  
CATALOG NUMBER: LD4D45BD010-EU4DR2540509027-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P748251  
 CATALOG NUMBER: LD4D45BD010-EU4DR2540509027-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89			89
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85			85
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82			82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			79
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77			77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74			74
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72			72
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69			69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1119366
5°	1042556
10°	743684
15°	438004
20°	272532
25°	149562
30°	68406
35°	25903
40°	11724
45°	7046
50°	2924
55°	1886
60°	1311
65°	879
70°	128
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7046 cd/sqm



TEST NUMBER: P748251

CATALOG NUMBER: LD4D45BD010-EU4DR2540509027-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	816.9	30.2
10°-20°	1106.5	41.0
20°-30°	585.5	21.7
30°-40°	144.6	5.4
40°-50°	35.3	1.3
50°-60°	9.3	0.3
60°-70°	3.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2508.9	92.9
0°-40°	2653.5	98.2
0°-60°	2698.0	99.9
0°-90°	2701.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2701.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10245	
5°	9506	817
15°	3872	1106
25°	1241	586
35°	194	145
45°	46	35
55°	10	9
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P748251

CATALOG NUMBER: LD4D45BD010-EU4DR2540509027-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10244.9
2.5°	10076.6
5°	9505.6
7.5°	8358.4
10°	6703.1
12.5°	5067.1
15°	3872.2
17.5°	3017.8
20°	2343.9
22.5°	1757.8
25°	1240.6
27.5°	832.0
30°	542.2
32.5°	329.9
35°	194.2
37.5°	118.9
40°	82.2
42.5°	62.9
45°	45.6
47.5°	27.6
50°	17.2
52.5°	12.5
55°	9.9
57.5°	7.8
60°	6.0
62.5°	4.7
65°	3.4
67.5°	1.3
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)